LPZM2A8

OBUDOWA METALOWA BEZ WYPOSAŻENIA, POKRYWA SZARA, 2 OTWORY

Charakterystyka ogólna

Kolor			Szary
Stopień ochrony według IEC			IP66 oraz IP67

Właściwości mechaniczne

Masa		g	458

Dane techniczne UL

Stopień ochrony według UL			NEMA 4X

Warunki otoczenia

Temperatura

Temperatura pracy			
	min.	°C	-25
	maks.	°C	+70
Temperatura składowania			
	min.	°C	-40
	maks.	°C	+85

Wymiary



a	b	c	d	e	f	g	h	l	k	ø
80	130	73	67	118	50	27	125	75	50	21

Certyfikaty i zgodność

Zgodność

CSA C22.2 n° 14
IEC/EN 60947-1
IEC/EN 60947-5-1
UL508

Certyfikaty

cULus
EAC

Klasyfikacja ETIM

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding

ETIM 8,0

EC000200 - Obudowa do urządzeń sterowniczych i sygnalizacyjnych

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding