



Metallic protection guard for LP4P...B5... LP4X159

Denumirea produsului

Denumirea tipului de produs

Caracteristici generale

Culoare

Galben

grad de protectie IEC

IP65

Conditii ambientale

Temperatura

Temperatura de Operare

min	°C	-25
max	°C	+70

Temperatura de depozitare

min	°C	-40
max	°C	+80

Dimensiuni

