



Mechanical features

Fixing	Screw		
Tightening torque for terminal lug	Nm	35	
Conductor section	IEC min	mm ²	16
	IEC max	mm ²	120
	AWG/kcmil min	6	
	AWG/kcmil max	kcmil	250kcmil
Weight	g	49	

UL technical data

UL Standard	UL98
-------------	------

Ambient conditions

Operating temperature	min	°C	-25
	max	°C	55
Storage temperature	min	°C	-40
	max	°C	70

Certifications and compliance

Compliance	IEC/EN/BS 60947-1
	IEC/EN/BS 60947-3

Certifications	cULus according to UL98 / CSA C22.2 n°4
----------------	---

ETIM classification

ETIM 8.0	EC002498 - Accessories/spare parts for low- voltage switch technology
----------	---