



**Mechanical features**

Fixing	Screw		
Tightening torque for terminal lug	Nm	35	
Conductor section	IEC min	mm <sup>2</sup>	16
	IEC max	mm <sup>2</sup>	120
	AWG/kcmil min	6	
	AWG/kcmil max	kcmil	250kcmil
Weight	g	100	

**UL technical data**

UL Standard	UL98
-------------	------

**Ambient conditions**

Operating temperature	min	°C	-25
	max	°C	55
Storage temperature	min	°C	-40
	max	°C	70

**Certifications and compliance**

Compliance	IEC/EN/BS 60947-1
	IEC/EN/BS 60947-3

Certifications	cULus according to UL98 / CSA C22.2 n°4
----------------	---

**ETIM classification**

ETIM 8.0	EC002498 - Accessories/spare parts for low- voltage switch technology
----------	---