# GLXM2D024

SPARE MOTOR OPERATOR FOR MOTORISED CHANGEOVER SWITCHES TYPE GLCMB0320…630D024



| | | | |
|---|---|---|---|
| **Motor data** | | | |
| Rated operational voltage | | V | 24VDC |
| Operating voltage range | | | 19.2…31.2VDC |
| Operating time | | | |
| | I-O, O-I | s | 0.45…0.83 |
| | I-O-II, II-O-I | s | 1.17…1.65 |
| Rated current (In) | | A | 0.80…1.10 |
| In-rush current | | A | 6.20…10.00 |
| Switching rate | | | |
| | Max continuous Cycles/min | | 1 |
| | Short time Cycles/min | | 10 |
| **Ambient conditions** | | | |
| Operating temperature | | | |
| | min | °C | -25 |
| | max | °C | +55 |
| Storage temperature | | | |
| | min | °C | -40 |
| | max | °C | +70 |
| Max altitude | | m | 3000 |


The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding