GLXM2E110

SPARE MOTOR OPERATOR FOR MOTORISED CHANGEOVER SWITCHES TYPE GLCMB0320…630E110



Motor data			
Rated operational voltage		V	110...125VAC/DC
Operating voltage range			77...165VAC/DC
Operating time			
	I-O, O-I	s	0.45…0.83
	I-O-II, II-O-I	s	1.13…1.58
Rated current (In)		A	0.75…1.08
In-rush current		A	4.50…7.50
Switching rate			
	Max continuous Cycles/min		1
	Short time Cycles/min		10
Ambient conditions			
Operating temperature			
	min	°C	-25
	max	°C	+55
Storage temperature			
	min	°C	-40
	max	°C	+70
Max altitude		m	3000

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding