GLXVS02

VOLTAGE SENSING CONNECTORS, 8-PIECES SET. FOR GLCMB0320…630…



Mechanical features			
Conductor section			
Weight		g	37
Ambient conditions			
Operating temperature			
	min	°C	-25
	max	°C	+55
Storage temperature			
	min	°C	-40
	max	°C	+70
Max altitude		m	3000
Resistance & Protection			
Pollution degree			3

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding