



Auxiliary contact characteristics

Rated insulation voltage U_i IEC/EN	V	1000
Rated impulse withstand voltage U_{imp}	kV	8
Tripping type	A	
Max. Delay		600ms

Operational characteristics

Rated operational voltage	V	220...460
Rated frequency	Hz	50/60

Mechanical features

Tightening torque for terminals			
	min	Nm	14
	max	Nm	14
	min	lbin	125
	max	lbin	125


Operating position	normal allowable	Vertical Any
--------------------	---------------------	-----------------


Terminals	type	Screw
Fixing		Screw

Ambient conditions

Temperature	Operating temperature		
	min	°C	-20
	max	°C	70

Dimensions





Wiring diagrams

Certifications and compliance

Compliance

IEC/EN/BS 60947-2

ETIM classification

EC000066 - Power contactor, AC switching