




Product designation	Bus module for EASY BRANCH		
Product type designation	EXS0000		
<b>Auxiliary supply Us</b>			
Auxiliary rated supply voltage DC	VDC	24	
Auxiliary operating voltage range DC			
	min	VDC	20.4
	Max	VDC	27.6
Power dissipation Max		W	5.5
<b>Mechanical features</b>			
Housing type	Polyamide		
Terminals type	Screw		
Conductor cross section			
	min	mm <sup>2</sup>	0.2
	Max	mm <sup>2</sup>	2.5
	min	AWG	12
	Max	AWG	24
Tightening torque (Max)			
		Nm	0.5
		lbin	4.5
Weight		g	90
<b>Ambient conditions</b>			
Temperature			
Operating temperature			
	min	°C	-20
	max	°C	+60
Storage temperature			
	min	°C	-30
	max	°C	+80
Relative humidity		%	<80
Maximum Pollution degree	2		
Overvoltage category	3		
Protection degree	IP20		
<b>Dimensions</b>			



### Certifications and compliance

#### Compliance

IEC/EN/BS 61000-6-2

IEC/EN/BS 61000-6-4

IEC/EN/BS 61010-1

#### Certificates

CE

cETLus

EAC

UKCA