



Product designation	Electronic current transformers for EASY BRANCH system
Product type designation	EXS3063
Type	Three-phase

Current inputs

Rated current (Ie)	A	63
--------------------	---	----

Current

IEC maximum (Imax)	A	63
--------------------	---	----

IEC rated (Iref-Ib)	A	10
---------------------	---	----

IEC start (Ist)	mA	20
-----------------	----	----

Insulations

Rated insulation voltage Ui IEC/EN	V	600
------------------------------------	---	-----

Mechanical features

Housing type	Polyamide
--------------	-----------

Terminals type	RJ45
----------------	------

Weight	g	140
--------	---	-----

Ambient conditions

Temperature				
-------------	--	--	--	--

Operating temperature	min	°C	-30
	max	°C	+70

Storage temperature	min	°C	-30
	max	°C	+80


Relative humidity	%	<80
-------------------	---	-----

Maximum Pollution degree	2
--------------------------	---

Overvoltage category	3
----------------------	---

Protection degree	IP20
-------------------	------

Dimensions



Certifications and compliance

Compliance	IEC/EN/BS 61000-6-2
	IEC/EN/BS 61000-6-4
	IEC/EN/BS 61010-1

Certificates

CE

cETLus

EAC

UKCA

ETIM classification

ETIM 8.0

EC002475 -
Current value
transformer