





Product designation	Engine protection controllers	
Product type designation	RGK30	
<b>Power supply</b>		
Rated battery voltage	V	12/24VDC
<b>Digital inputs</b>		
Digital input type	3 neg.+ 1 pos.	
<b>"W"/AC/PICK-UP speed inputs</b>		
"W"/AC/PICK-UP speed input type	"W"	
<b>Relay outputs</b>		
Type of output contact	2 (relay)	
<b>Mechanical features</b>		
Weight	g	160
<b>Ambient conditions</b>		
Protection degree	IP40	
<b>Dimensions</b>		



**Wiring diagrams**



## Certifications and compliance

### Compliance

CSA C22.2 n° 14

EN 55011

IEC/EN 61000-6-2

IEC/EN 61010-1

UL 508

### Certificates

EAC

UL Listed for USA and Canada (cULus-File E93601)

## ETIM classification

ETIM 8.0

EC000236 - PLC  
CPU-module