




Product designation	SOCKET		
Product type designation	HR1XS024S		
Contact characteristics			
Rated insulation voltage U_i IEC/EN	V	250	
Rated impulse withstand voltage U_{imp}	kV	4	
Coil characteristics			
Relay control voltage + socket	V	12...24VAC/DC	
Mechanical features			
Socket screw tightening tool (cross / flat blade)	Phillips 0/3.5mm		
Conductor section			
	AWG/Kcmil		
		min	20
		max	16
	IEC		
		min	mm ² 0.5
		max	mm ² 1.5
Fixing	On 35mm DIN rail		
Dimensions			




Wiring diagrams



12 NC

11 COM

14 NO



Certifications and compliance

Compliance

IEC/EN 61810

Certificates

CSA

cURus

EAC

ETIM classification

ETIM 8.0

EC001456 -
 Relay socket