



Product designation SOCKET
Product type designation HR5XS21S

Contact characteristics

Rated insulation voltage U_i IEC/EN	V	250
Rated impulse withstand voltage U_{imp}	kV	4


Mechanical features

Socket screw tightening tool (cross / flat blade) Phillips 1/4.5mm

Conductor section	AWG/Kcmil	min	20	
		max	14	
	IEC	min	mm ²	0.5
		max	mm ²	2.5


Fixing On 35mm DIN rail

Dimensions



A: 60mm (2.36") with HR3X88
70mm (2.75") with XR5X88

Wiring diagrams



Certifications and compliance

Compliance	IEC/EN 61810
Certificates	CSA
	cURus
	EAC

ETIM classification

ETIM 8.0	EC001456 - Relay socket
----------	-------------------------