



Product designation **SOCKET**
Product type designation **HR6XS41S**

Contact characteristics

Rated insulation voltage U_i IEC/EN	V	250
Rated impulse withstand voltage U_{imp}	kV	4


Mechanical features

Socket screw tightening tool (cross / flat blade) **Phillips 1/4.5mm**


Conductor section	AWG/Kcmil	min	20
		max	14
	IEC	min	mm ² 0.5
		max	mm ² 2.5

Fixing **On 35mm DIN rail**

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

IEC/EN 61810

Certificates

CSA

cURus

EAC

ETIM classification

ETIM 8.0

EC001456 -
Relay socket