



Product designation
 Product type designation

Probe
 SCM

Connections

Terminals type

Threaded rod
 with nut

Ambient conditions

Temperature

Operating temperature

max °C +100

Maximum operating pressure


bar 10

Housing

Weight

g 60

Dimensions



TYPE	L
SCM04	43 (1.69")
SCM50	500 (19.68")
SCM100	1000 (39.37")

Certifications and compliance

Compliance

/

Certificates

EAC

ETIM classification

ETIM 8.0

EC010106 -
 Liquid level
 sensor