



Product designation
Product type designation

Description

Accessories for

Undervoltage trip
P5X14E230UL
Undervoltage trip
releases for UL
certified MCCBs.
Accessories for
UL-compliant
MCCBs

Operational characteristics

Rated supply voltage AC	VAC	220...240
Rated supply voltage DC	VDC	250
Rated frequency	Hz	45...65
Holding consumption	VA	1.21
Release voltage	Us	35...70
Operating voltage	US	85...110
Average opening time	ms	50

Mechanical features

Tightening torque for terminals

min	Nm	0.8
max	Nm	1
min	lbin	7
max	lbin	9

Conductor section

AWG/Kcmil

min	20
max	16

Flexible w/o lug conductor section

min	mm ²	0.5
max	mm ²	1.5

Flexible c/w lug conductor section

min	mm ²	0.5
max	mm ²	1.5

Terminals

type	Screw
tool	PZ2

Weight

g	50
---	----



Wiring diagrams

Certifications and compliance

Certificates

cULus

ETIM classification

EC000066 - Power contactor, AC switching