



Mounting adapter with contact element for LPS and LPF LPXE10M

Product designation

Product type designation

Electrical characteristics

IEC Conventional free air thermal current I _{th}	A	10
UL/CSA and IEC/EN 60947-5-1 designation	A300 Q300	
Operating current AC15		
	12V	A 6
	24V	A 6
	48V	A 6
	120V	A 6
	240V	A 3

Operating current DC13

	12V	A	0.55
	24V	A	0.55
	48V	A	0.55
	125V	A	0.55
	250V	A	0.27

Contact resistance	mΩ	≤20
--------------------	----	-----

Mechanical features

Mechanical life	cycles	1000000
Tightening torque for terminals max	Nm	1

Terminals screw	Clamp screw with washer
-----------------	-------------------------

Mounting adapter	Included with contacts
------------------	------------------------

UL technical data

UL degree of protection	Type 1, 2, 3R, 4, 4X, 12, 12K
-------------------------	-------------------------------

Ambient conditions

Temperature

Operating temperature

min	°C	-25
max	°C	+60

Storage temperature

min	°C	-40
max	°C	+70

Certifications and compliance

Compliance

CSA C22.2 n° 14
IEC/EN/BS 60947-1
IEC/EN/BS 60947-5-1
UL508

Certificates

cULus

ETIM classification

ETIM 8.0

EC002498 -
Accessories/spare
parts for low-
voltage switch
technology