



Enclosures with cut-outs for Ø22mm units - with multiholes for 16 actuators LPZM

Product designation

Product type designation

General characteristics

Colour Grey

IEC degree of protection IP66 and IP67

Mechanical features

Weight g 1650

UL technical data

UL degree of protection NEMA 4X

Ambient conditions

Temperature


Operating temperature

min °C -25
max °C +70

Storage temperature

min °C -40
max °C +85

Dimensions



Certifications and compliance

Compliance

IEC/EN 60947-5-1

Certificates

cULus
EAC

ETIM classification

ETIM 8.0

EC000200 -
Enclosure for control circuit devices