




Product designation	Enclosures		
Product type designation	LPZM		
General characteristics			
Colour	Grey		
IEC degree of protection	IP66 and IP67		
Mechanical features			
Weight	g	462	
UL technical data			
UL degree of protection	NEMA 4X		
Ambient conditions			
Temperature			
Operating temperature	min	°C	-25
	max	°C	+70
Storage temperature	min	°C	-40
	max	°C	+85

Dimensions



Certifications and compliance

Compliance	IEC/EN 60947-5-1
Certificates	cULus EAC

ETIM classification

ETIM 8.0

EC000200 -
Enclosure for
control circuit
devices