




Product designation	Enclosures
Product type designation	LPZM
General characteristics	
Colour	Grey
IEC degree of protection	IP66 and IP67
Mechanical features	
Weight	g 600
UL technical data	
UL degree of protection	NEMA 4X
Ambient conditions	
Temperature	
Operating temperature	min °C -25 max °C +70
Storage temperature	min °C -40 max °C +85

Dimensions



Certifications and compliance

Compliance

IEC/EN 60947-5-1

Certificates

cULus

EAC

ETIM classification

ETIM 8.0

EC000200 -
Enclosure for
control circuit
devices