



Enclosures with cut-outs for Ø22mm units - with multiholes for 4 actuators LPZM

Product designation

Product type designation

General characteristics

Colour Grey

IEC degree of protection IP66 and IP67

Mechanical features

Weight g 570

UL technical data

UL degree of protection NEMA 4X

Ambient conditions

Temperature


Operating temperature

	min	°C	-25
	max	°C	+70

Storage temperature

	min	°C	-40
	max	°C	+85

Dimensions



Certifications and compliance

Compliance

IEC/EN 60947-5-1

Certificates

cULus

EAC

ETIM classification

ETIM 8.0

EC000200 -
Enclosure for
control circuit
devices