





| | | |
|---|-----|---------|
| Number of poles | Nr. | 1 |
| Operating voltage type | | AC |
| Contact characteristics | | |
| IEC Conventional free air thermal current I _{th} | A | 80 |
| Mechanical features | | |
| Tightening torque for terminals | | |
| | min | Nm 5 |
| | max | Nm 6 |
| | min | lbin 45 |
| | max | lbin 54 |

Dimensions



Wiring diagrams

Fourth pole add on
GAX42... **GAX41...**



Certifications and compliance

Compliance

CSA C22.2
IEC/EN 60947-1
IEC/EN 60947-3
UL508
UL98

Certifications

CCC
CSA C22.2 n°4
cULus according to UL98
EAC

ETIM classification

ETIM 8.0

EC002498 -
Accessories/spare
parts for low-
voltage switch
technology