



Auxiliary  
contactor  
BGF00

Product designation

Product type designation

**Contact characteristics**


Number of poles	Nr.	4
Rated insulation voltage $U_i$ IEC/EN	V	690
Rated impulse withstand voltage $U_{imp}$	kV	6
Operational frequency	min	Hz 25
	max	Hz 400
IEC Conventional free air thermal current $I_{th}$	A	10
Short-time allowable current for 10s (IEC/EN60947-1)	A	0
Protection fuse	gG (IEC)	A 16
Tightening torque for terminals	min	Nm 0.8
	max	Nm 1
	min	Ibin 9
	max	Ibin 9
Tightening torque for coil terminal	min	Nm 0.8
	max	Nm 1
	min	Ibin 9
	max	Ibin 9
Max number of wires simultaneously connectable	Nr.	2
Conductor section	AWG/Kcmil	
	max	12
Flexible w/o lug conductor section	min	mm <sup>2</sup> 0.75
	max	mm <sup>2</sup> 2.5
Flexible c/w lug conductor section	min	mm <sup>2</sup> 1.5
	max	mm <sup>2</sup> 2.5
Flexible with insulated spade lug conductor section	min	mm <sup>2</sup> 1.5
	max	mm <sup>2</sup> 2.5
Power terminal protection according to IEC/EN 60529		IP20 when properly wired

**Mechanical features**


Operating position	normal	Vertical plan
	allowable	±30°
Fixing		Screw / DIN rail 35mm
Weight	g	180

Conductor section	AWG/kcmil conductor section			max	12
<b>Auxiliary contact characteristics</b>					
Thermal current I <sub>th</sub>				A	10
IEC/EN 60947-5-1 designation				A600 - Q600	
Operating current AC15				230V	A 3
				400V	A 1.9
				500V	A 1.4
Operating current DC12				110V	A 2.9
Operating current DC13				24V	A 2.9
				48V	A 1.4
				60V	A 1.1
				125V	A 0.3
				220V	A 0.1
				600V	A 0.6
<b>Operations</b>					
Mechanical life				cycles	20000000
<b>Safety related data</b>					
Performance level B10d according to EN/ISO 13489-1				mechanical load	cycles 20000000
Mirror contacts according to IEC/EN 60947-4-1				YES	
EMC compatibility				yes	
<b>AC coil operating</b>					
Rated AC voltage at 50/60Hz				V	230
AC operating voltage	of 50/60Hz coil powered at 50Hz			pick-up	
				min	%Us 75
				max	%Us 115
	drop-out				
				min	%Us 20
				max	%Us 55
	of 50/60Hz coil powered at 60Hz			pick-up	
				min	%Us 80
				max	%Us 115
	drop-out				
				min	%Us 20
				max	%Us 55
AC average coil consumption at 20°C	of 50/60Hz coil powered at 50Hz			in-rush	VA 30
				holding	VA 4
	of 50/60Hz coil powered at 60Hz			in-rush	VA 25
				holding	VA 3
	of 60Hz coil powered at 60Hz			in-rush	VA 30
				holding	VA 4

Dissipation at holding ≤20°C 50Hz	W	0.95
<b>Max cycles frequency</b>		
Mechanical operation	cycles/h	3600
<b>Operating times</b>		
Average time for Us control		
in AC		
Closing NO	min	ms 12
	max	ms 21
Opening NO	min	ms 9
	max	ms 18
Closing NC	min	ms 17
	max	ms 26
Opening NC	min	ms 7
	max	ms 17
in DC		
Closing NO	min	ms 18
	max	ms 25
Opening NO	min	ms 2
	max	ms 3
Closing NC	min	ms 3
	max	ms 5
Opening NC	min	ms 11
	max	ms 17
<b>UL technical data</b>		
Contact rating of auxiliary contacts according to UL		A600 - Q600
<b>Ambient conditions</b>		
Temperature		
Operating temperature		
	min	°C -50
	max	°C +70
Storage temperature		
	min	°C -60
	max	°C +80
Max altitude	m	3000
<b>Resistance &amp; Protection</b>		
Pollution degree		3
<b>Dimensions</b>		



**Wiring diagrams**



**Certifications and compliance**

**Compliance**

- CSA C22.2 n° 60947-1
- CSA C22.2 n° 60947-5-1
- IEC/EN 60947-1
- IEC/EN 60947-5-1
- UL 60947-1
- UL 60947-5-1

**Certificates**

- CCC
- cULus
- EAC

**ETIM classification**

ETIM 8.0

EC000196 -  
Contactor relay