



|  |   |    |     |                 |
|--|---|----|-----|-----------------|
| Product designation  |   |    |     | Power contactor |
| Product type designation   |   |    |     | BGF09           |
| <b>Contact characteristics</b>   |   |    |     |                 |
| Number of poles  | Nr.   |    |     | 3               |
| Rated insulation voltage $U_i$ IEC/EN  | V   |    |     | 690             |
| Rated impulse withstand voltage $U_{imp}$                                      | kV  |    |     | 6               |
| Operational frequency  | min   | Hz | 25  |                 |
|  | max   | Hz | 400 |                 |
| IEC Conventional free air thermal current $I_{th}$                             | A   |    |     | 20              |
| Operational current $I_e$  | AC-1 ( $\leq 40^\circ\text{C}$ )                  | A  | 20  |                 |
|  | AC-1 ( $\leq 55^\circ\text{C}$ )                  | A  | 18  |                 |
|  | AC-1 ( $\leq 70^\circ\text{C}$ )                  | A  | 15  |                 |
|  | AC-3 ( $\leq 440\text{V} \leq 55^\circ\text{C}$ ) | A  | 9   |                 |
|  | AC-4 (400V)                                       | A  | 4   |                 |
| Rated operational power AC-3 ( $T \leq 55^\circ\text{C}$ )                     | 230V  | kW | 2.2 |                 |
|  | 400V  | kW | 4   |                 |
|  | 415V  | kW | 4.3 |                 |
|  | 440V  | kW | 4.5 |                 |
|  | 500V  | kW | 5   |                 |
|  | 690V  | kW | 5   |                 |
| Rated operational power AC-1 ( $T \leq 40^\circ\text{C}$ )                     | 230V  | kW | 8   |                 |
|  | 400V  | kW | 14  |                 |
|  | 500V  | kW | 16  |                 |
|  | 690V  | kW | 22  |                 |
| IEC max current $I_e$ in DC1 with $L/R \leq 1\text{ms}$ with 1 poles in series | $\leq 24\text{V}$                                 | A  | 12  |                 |
|  | 48V   | A  | 10  |                 |
|  | 75V   | A  | 4   |                 |
|  | 110V  | A  | 3   |                 |
|  | 220V  | A  | -   |                 |
| IEC max current $I_e$ in DC1 with $L/R \leq 1\text{ms}$ with 2 poles in series | $\leq 24\text{V}$                                 | A  | 15  |                 |
|  | 48V   | A  | 14  |                 |
|  | 75V   | A  | 9   |                 |
|  | 110V  | A  | 8   |                 |
|  | 220V  | A  | -   |                 |
| IEC max current $I_e$ in DC1 with $L/R \leq 1\text{ms}$ with 3 poles in series | $\leq 24\text{V}$                                 | A  | 16  |                 |
|  | 48V   | A  | 16  |                 |
|  | 75V   | A  | 10  |                 |
|  | 110V  | A  | 10  |                 |

|  |                 |                  |      |
|--|-----------------|------------------|------|
|  | 220V            | A                | 2    |
| IEC max current I <sub>e</sub> in DC1 with L/R ≤ 1ms with 4 poles in series      | ≤24V            | A                | 16   |
|  | 48V             | A                | 16   |
|  | 75V             | A                | 10   |
|  | 110V            | A                | 10   |
|  | 220V            | A                | 2    |
| IEC max current I <sub>e</sub> in DC3-DC5 with L/R ≤ 15ms with 1 poles in series | ≤24V            | A                | 7    |
|  | 48V             | A                | 6    |
|  | 75V             | A                | 2    |
|  | 110V            | A                | 1    |
|  | 220V            | A                | –    |
| IEC max current I <sub>e</sub> in DC3-DC5 with L/R ≤ 15ms with 2 poles in series | ≤24V            | A                | 8    |
|  | 48V             | A                | 8    |
|  | 75V             | A                | 5    |
|  | 110V            | A                | 4    |
|  | 220V            | A                | –    |
| IEC max current I <sub>e</sub> in DC3-DC5 with L/R ≤ 15ms with 3 poles in series | ≤24V            | A                | 10   |
|  | 48V             | A                | 10   |
|  | 75V             | A                | 6    |
|  | 110V            | A                | 5    |
|  | 220V            | A                | 0,8  |
| IEC max current I <sub>e</sub> in DC3-DC5 with L/R ≤ 15ms with 4 poles in series | ≤24V            | A                | 10   |
|  | 48V             | A                | 10   |
|  | 75V             | A                | 6    |
|  | 110V            | A                | 5    |
|  | 220V            | A                | 0,8  |
| Short-time allowable current for 10s (IEC/EN60947-1)                             |                 | A                | 96   |
| Protection fuse  | gG (IEC)        | A                | 20   |
|  | aM (IEC)        | A                | 10   |
| Making capacity (RMS value)  |                 | A                | 92   |
| Breaking capacity at voltage   | 440V            | A                | 72   |
|  | 500V            | A                | 72   |
|  | 690V            | A                | 72   |
| Resistance per pole (average value)  |                 | mΩ               | 10   |
| Power dissipation per pole (average value)                                       | I <sub>th</sub> | W                | 4    |
|  | AC-3            | W                | 0.81 |
| Tightening torque for terminals  | min             | Nm               | 0.8  |
|  | max             | Nm               | 1    |
|  | min             | I <sub>bin</sub> | 9    |
|  | max             | I <sub>bin</sub> | 9    |
| Tightening torque for coil terminal  | min             | Nm               | 0.8  |
|  | max             | Nm               | 1    |
|  | min             | I <sub>bin</sub> | 9    |

|   |                             |                  |                 |                          |
|---|-----------------------------|------------------|-----------------|--------------------------|
|   |                             | max              | lbin            | 9                        |
| Max number of wires simultaneously connectable      |                             |                  | Nr.             | 2                        |
| Conductor section                                   | AWG/Kcmil                   | max              |                 | 12                       |
| Flexible w/o lug conductor section                  |                             | min              | mm <sup>2</sup> | 0.75                     |
|   |                             | max              | mm <sup>2</sup> | 2.5                      |
| Flexible c/w lug conductor section                  |                             | min              | mm <sup>2</sup> | 1.5                      |
|   |                             | max              | mm <sup>2</sup> | 2.5                      |
| Flexible with insulated spade lug conductor section |                             | min              | mm <sup>2</sup> | 1.5                      |
|   |                             | max              | mm <sup>2</sup> | 2.5                      |
| Power terminal protection according to IEC/EN 60529 |                             |                  |                 | IP20 when properly wired |
| <b>Mechanical features</b>                          |                             |                  |                 |                          |
| Operating position                                  |                             | normal allowable |                 | Vertical plan ±30°       |
| Fixing  |                             |                  |                 | Screw / DIN rail 35mm    |
| Weight  |                             |                  | g               | 180                      |
| Conductor section                                   | AWG/kcmil conductor section | max              |                 | 12                       |
| <b>Auxiliary contact characteristics</b>            |                             |                  |                 |                          |
| Thermal current I <sub>th</sub>                     |                             |                  | A               | 10                       |
| IEC/EN 60947-5-1 designation                        |                             |                  |                 | A600 - Q600              |
| Operating current AC15                              |                             | 230V             | A               | 3                        |
|   |                             | 400V             | A               | 1.9                      |
|   |                             | 500V             | A               | 1.4                      |
| Operating current DC12                              |                             | 110V             | A               | 2.9                      |
| Operating current DC13                              |                             | 24V              | A               | 2.9                      |
|   |                             | 48V              | A               | 1.4                      |
|   |                             | 60V              | A               | 1.1                      |
|   |                             | 125V             | A               | 0.3                      |
|   |                             | 220V             | A               | 0.1                      |
|   |                             | 600V             | A               | 0.6                      |
| <b>Operations</b>                                   |                             |                  |                 |                          |
| Mechanical life                                     |                             |                  | cycles          | 20000000                 |
| Electrical life                                     |                             |                  | cycles          | 500000                   |
| <b>Safety related data</b>                          |                             |                  |                 |                          |
| Performance level B10d according to EN/ISO 13489-1  |                             | rated load       | cycles          | 500000                   |
|   |                             | mechanical load  | cycles          | 20000000                 |
| Mirror contacts according to IEC/EN 60947-4-1       |                             |                  |                 | yes                      |
| EMC compatibility                                   |                             |                  |                 | yes                      |
| <b>AC coil operating</b>                            |                             |                  |                 |                          |
| Rated AC voltage at 60Hz                            |                             |                  | V               | 230                      |

AC operating voltage

of 60Hz coil powered at 60Hz  
pick-up

|     |     |     |
|-----|-----|-----|
| min | %Us | 75  |
| max | %Us | 115 |

drop-out

|     |     |    |
|-----|-----|----|
| min | %Us | 20 |
| max | %Us | 55 |

AC average coil consumption at 20°C

of 50/60Hz coil powered at 50Hz

|         |    |    |
|---------|----|----|
| in-rush | VA | 30 |
| holding | VA | 4  |

of 50/60Hz coil powered at 60Hz

|         |    |    |
|---------|----|----|
| in-rush | VA | 25 |
| holding | VA | 3  |

of 60Hz coil powered at 60Hz

|         |    |    |
|---------|----|----|
| in-rush | VA | 30 |
| holding | VA | 4  |

Dissipation at holding ≤20°C 50Hz

|   |      |
|---|------|
| W | 0.95 |
|---|------|

Max cycles frequency

Mechanical operation

|          |      |
|----------|------|
| cycles/h | 3600 |
|----------|------|

Operating times

Average time for Us control

in AC

Closing NO

|     |    |    |
|-----|----|----|
| min | ms | 12 |
| max | ms | 21 |

Opening NO

|     |    |    |
|-----|----|----|
| min | ms | 9  |
| max | ms | 18 |

Closing NC

|     |    |    |
|-----|----|----|
| min | ms | 17 |
| max | ms | 26 |

Opening NC

|     |    |    |
|-----|----|----|
| min | ms | 7  |
| max | ms | 17 |

in DC

Closing NO

|     |    |    |
|-----|----|----|
| min | ms | 18 |
| max | ms | 25 |

Opening NO

|     |    |   |
|-----|----|---|
| min | ms | 2 |
| max | ms | 3 |

Closing NC

|     |    |   |
|-----|----|---|
| min | ms | 3 |
| max | ms | 5 |

Opening NC

|     |    |    |
|-----|----|----|
| min | ms | 11 |
| max | ms | 17 |

UL technical data

Full-load current (FLA) for three-phase AC motor

|         |   |     |
|---------|---|-----|
| at 480V | A | 7.6 |
| at 600V | A | 6.1 |

Yielded mechanical performance

for single-phase AC motor

|          |    |     |
|----------|----|-----|
| 110/120V | HP | 0.5 |
| 230V     | HP | 1.5 |

for three-phase AC motor

|          |    |   |
|----------|----|---|
| 200/208V | HP | 2 |
| 220/230V | HP | 3 |
| 460/480V | HP | 5 |
| 575/600V | HP | 5 |

General USE

Contactor

|            |   |    |
|------------|---|----|
| AC current | A | 20 |
|------------|---|----|

Short-circuit protection fuse, 600V  
High fault

|                       |    |     |
|-----------------------|----|-----|
| Short circuit current | kA | 100 |
| Fuse rating           | A  | 30  |
| Fuse class            |    | J   |

Standard fault

|                       |    |    |
|-----------------------|----|----|
| Short circuit current | kA | 5  |
| Fuse rating           | A  | 30 |

Contact rating of auxiliary contacts according to UL

A600 - Q600

Ambient conditions

Temperature

Operating temperature

|     |    |     |
|-----|----|-----|
| min | °C | -50 |
| max | °C | +70 |

Storage temperature

|     |    |     |
|-----|----|-----|
| min | °C | -60 |
| max | °C | +80 |

Max altitude


m 3000

Resistance & Protection

Pollution degree

3

Dimensions



Wiring diagrams



### Certifications and compliance

#### Compliance

CSA C22.2 n° 60947-1

CSA C22.2 n° 60947-4-1

IEC/EN 60947-1

IEC/EN 60947-4-1

UL 60947-1

UL 60947-4-1

#### Certificates

CCC

cULus

EAC

### ETIM classification

ETIM 8.0

EC000066 -  
Power contactor,  
AC switching