



Product designation  
Product type designation

Power contactor  
BGF09

**Contact characteristics**

|  |   |        |
|--|---|--------|
| Number of poles  | Nr.   | 3      |
| Rated insulation voltage $U_i$ IEC/EN  | V   | 690    |
| Rated impulse withstand voltage $U_{imp}$                                      | kV  | 6      |
| Operational frequency  | min   | Hz 25  |
|  | max   | Hz 400 |
| IEC Conventional free air thermal current $I_{th}$                             | A   | 20     |
| Operational current $I_e$  | AC-1 ( $\leq 40^\circ\text{C}$ )                  | A 20   |
|  | AC-1 ( $\leq 55^\circ\text{C}$ )                  | A 18   |
|  | AC-1 ( $\leq 70^\circ\text{C}$ )                  | A 15   |
|  | AC-3 ( $\leq 440\text{V} \leq 55^\circ\text{C}$ ) | A 9    |
|  | AC-4 (400V)                                       | A 4    |
| Rated operational power AC-3 ( $T \leq 55^\circ\text{C}$ )                     | 230V  | kW 2.2 |
|  | 400V  | kW 4   |
|  | 415V  | kW 4.3 |
|  | 440V  | kW 4.5 |
|  | 500V  | kW 5   |
|  | 690V  | kW 5   |
| Rated operational power AC-1 ( $T \leq 40^\circ\text{C}$ )                     | 230V  | kW 8   |
|  | 400V  | kW 14  |
|  | 500V  | kW 16  |
|  | 690V  | kW 22  |
| IEC max current $I_e$ in DC1 with $L/R \leq 1\text{ms}$ with 1 poles in series | $\leq 24\text{V}$                                 | A 12   |
|  | 48V   | A 10   |
|  | 75V   | A 4    |
|  | 110V  | A 3    |
|  | 220V  | A –    |
| IEC max current $I_e$ in DC1 with $L/R \leq 1\text{ms}$ with 2 poles in series | $\leq 24\text{V}$                                 | A 15   |
|  | 48V   | A 14   |
|  | 75V   | A 9    |
|  | 110V  | A 8    |
|  | 220V  | A –    |
| IEC max current $I_e$ in DC1 with $L/R \leq 1\text{ms}$ with 3 poles in series | $\leq 24\text{V}$                                 | A 16   |
|  | 48V   | A 16   |
|  | 75V   | A 10   |
|  | 110V  | A 10   |
|  | 220V  | A 2    |

IEC max current Ie in DC1 with L/R ≤ 1ms with 4 poles in series

|      |   |    |
|------|---|----|
| ≤24V | A | 16 |
| 48V  | A | 16 |
| 75V  | A | 10 |
| 110V | A | 10 |
| 220V | A | 2  |

IEC max current Ie in DC3-DC5 with L/R ≤ 15ms with 1 poles in series

|      |   |   |
|------|---|---|
| ≤24V | A | 7 |
| 48V  | A | 6 |
| 75V  | A | 2 |
| 110V | A | 1 |
| 220V | A | – |

IEC max current Ie in DC3-DC5 with L/R ≤ 15ms with 2 poles in series

|      |   |   |
|------|---|---|
| ≤24V | A | 8 |
| 48V  | A | 8 |
| 75V  | A | 5 |
| 110V | A | 4 |
| 220V | A | – |

IEC max current Ie in DC3-DC5 with L/R ≤ 15ms with 3 poles in series

|      |   |     |
|------|---|-----|
| ≤24V | A | 10  |
| 48V  | A | 10  |
| 75V  | A | 6   |
| 110V | A | 5   |
| 220V | A | 0,8 |

IEC max current Ie in DC3-DC5 with L/R ≤ 15ms with 4 poles in series

|      |   |     |
|------|---|-----|
| ≤24V | A | 10  |
| 48V  | A | 10  |
| 75V  | A | 6   |
| 110V | A | 5   |
| 220V | A | 0,8 |

Short-time allowable current for 10s (IEC/EN60947-1)

|   |    |
|---|----|
| A | 96 |
|---|----|

Protection fuse

|          |   |    |
|----------|---|----|
| gG (IEC) | A | 20 |
| aM (IEC) | A | 10 |

Making capacity (RMS value)

|   |    |
|---|----|
| A | 92 |
|---|----|

Breaking capacity at voltage

|      |   |    |
|------|---|----|
| 440V | A | 72 |
| 500V | A | 72 |
| 690V | A | 72 |

Resistance per pole (average value)

|    |    |
|----|----|
| mΩ | 10 |
|----|----|

Power dissipation per pole (average value)

|      |   |      |
|------|---|------|
| Ith  | W | 4    |
| AC-3 | W | 0.81 |

Tightening torque for terminals

|     |      |     |
|-----|------|-----|
| min | Nm   | 0.8 |
| max | Nm   | 1   |
| min | Ibin | 9   |
| max | Ibin | 9   |

Tightening torque for coil terminal

|     |      |     |
|-----|------|-----|
| min | Nm   | 0.8 |
| max | Nm   | 1   |
| min | Ibin | 9   |
| max | Ibin | 9   |

|   |                             |                    |          |
|---|-----------------------------|--------------------|----------|
| Max number of wires simultaneously connectable      | Nr.                         | 2                  |          |
| Conductor section                                   | AWG/Kcmil                   |                    |          |
|   | max                         | 12                 |          |
| Flexible w/o lug conductor section                  | min                         | mm <sup>2</sup>    | 0.75     |
|   | max                         | mm <sup>2</sup>    | 2.5      |
| Flexible c/w lug conductor section                  | min                         | mm <sup>2</sup>    | 1.5      |
|   | max                         | mm <sup>2</sup>    | 2.5      |
| Flexible with insulated spade lug conductor section | min                         | mm <sup>2</sup>    | 1.5      |
|   | max                         | mm <sup>2</sup>    | 2.5      |
| Power terminal protection according to IEC/EN 60529 | IP20 when properly wired    |                    |          |
| <b>Mechanical features</b>                          |                             |                    |          |
| Operating position                                  | normal allowable            | Vertical plan ±30° |          |
| Fixing  | Screw / DIN rail 35mm       |                    |          |
| Weight  | g                           | 220                |          |
| Conductor section                                   | AWG/kcmil conductor section |                    |          |
|   | max                         | 12                 |          |
| <b>Auxiliary contact characteristics</b>            |                             |                    |          |
| Thermal current I <sub>th</sub>                     | A                           | 10                 |          |
| IEC/EN 60947-5-1 designation                        | A600 - Q600                 |                    |          |
| Operating current AC15                              | 230V                        | A                  | 3        |
|   | 400V                        | A                  | 1.9      |
|   | 500V                        | A                  | 1.4      |
| Operating current DC12                              | 110V                        | A                  | 2.9      |
| Operating current DC13                              | 24V                         | A                  | 2.9      |
|   | 48V                         | A                  | 1.4      |
|   | 60V                         | A                  | 1.1      |
|   | 125V                        | A                  | 0.3      |
|   | 220V                        | A                  | 0.1      |
|   | 600V                        | A                  | 0.6      |
| <b>Operations</b>                                   |                             |                    |          |
| Mechanical life                                     | cycles                      | 20000000           |          |
| Electrical life                                     | cycles                      | 500000             |          |
| <b>Safety related data</b>                          |                             |                    |          |
| Performance level B10d according to EN/ISO 13489-1  | rated load                  | cycles             | 500000   |
|   | mechanical load             | cycles             | 20000000 |
| Mirror contacts according to IEC/EN 60947-4-1       | yes                         |                    |          |
| EMC compatibility                                   | yes                         |                    |          |
| <b>DC coil operating</b>                            |                             |                    |          |
| DC rated control voltage                            | V                           | 12                 |          |
| DC operating voltage                                |                             |                    |          |

|          |     |     |     |
|----------|-----|-----|-----|
| pick-up  | min | %Us | 75  |
|          | max | %Us | 115 |
| <hr/>    |     |     |     |
| drop-out | min | %Us | 10  |
|          | max | %Us | 25  |

Average coil consumption  $\leq 20^{\circ}\text{C}$

|         |   |     |
|---------|---|-----|
| in-rush | W | 3.2 |
| holding | W | 3.2 |

**Max cycles frequency**

Mechanical operation cycles/h 3600

**Operating times**

Average time for Us control

in AC

Closing NO

|     |    |    |
|-----|----|----|
| min | ms | 12 |
| max | ms | 21 |

Opening NO

|     |    |    |
|-----|----|----|
| min | ms | 9  |
| max | ms | 18 |

Closing NC

|     |    |    |
|-----|----|----|
| min | ms | 17 |
| max | ms | 26 |

Opening NC

|     |    |    |
|-----|----|----|
| min | ms | 7  |
| max | ms | 17 |

in DC

Closing NO

|     |    |    |
|-----|----|----|
| min | ms | 18 |
| max | ms | 25 |

Opening NO

|     |    |   |
|-----|----|---|
| min | ms | 2 |
| max | ms | 3 |

Closing NC

|     |    |   |
|-----|----|---|
| min | ms | 3 |
| max | ms | 5 |

Opening NC

|     |    |    |
|-----|----|----|
| min | ms | 11 |
| max | ms | 17 |

**UL technical data**

Full-load current (FLA) for three-phase AC motor

|         |   |     |
|---------|---|-----|
| at 480V | A | 7.6 |
| at 600V | A | 6.1 |

Yielded mechanical performance

for single-phase AC motor

|          |    |     |
|----------|----|-----|
| 110/120V | HP | 0.5 |
| 230V     | HP | 1.5 |

for three-phase AC motor

|          |    |   |
|----------|----|---|
| 200/208V | HP | 2 |
| 220/230V | HP | 3 |
| 460/480V | HP | 5 |
| 575/600V | HP | 5 |

General USE

Contactor

|  |                       |    |             |
|--|-----------------------|----|-------------|
|  | AC current            | A  | 20          |
| Short-circuit protection fuse, 600V<br>High fault    | Short circuit current | kA | 100         |
|  | Fuse rating           | A  | 30          |
|  | Fuse class            |    | J           |
| Standard fault                                       | Short circuit current | kA | 5           |
|  | Fuse rating           | A  | 30          |
| Contact rating of auxiliary contacts according to UL |                       |    | A600 - Q600 |

**Ambient conditions**

Temperature

Operating temperature

|     |    |     |
|-----|----|-----|
| min | °C | -50 |
| max | °C | +70 |

Storage temperature

|     |    |     |
|-----|----|-----|
| min | °C | -60 |
| max | °C | +80 |

Max altitude


|   |      |
|---|------|
| m | 3000 |
|---|------|

**Resistance & Protection**


Pollution degree

3

**Dimensions**



**Wiring diagrams**



### Certifications and compliance

#### Compliance

CSA C22.2 n° 60947-1

CSA C22.2 n° 60947-4-1

IEC/EN 60947-1

IEC/EN 60947-4-1

UL 60947-1

UL 60947-4-1

#### Certificates

CCC

cULus

EAC

### ETIM classification

ETIM 8.0

EC000066 -  
Power contactor,  
AC switching