



Product designation				Auxiliary contact
Product type designation				11BGX10
Contact characteristics				
Number of poles	Nr.			4
Rated insulation voltage U_i IEC/EN	V			690
Rated impulse withstand voltage U_{imp}	kV			6
IEC Conventional free air thermal current I_{th}	A			10
Tightening torque for terminals	min	Nm	0.8	
	max	Nm	1	
	min	lbin	9	
	max	lbin	9	
Tightening torque for coil terminal	min	lbin	9	
	max	lbin	9	
Max number of wires simultaneously connectable	Nr.			2
Conductor section	AWG/Kcmil			
		max	12	
	Flexible w/o lug conductor section			
	min	mm ²	0.75	
	max	mm ²	2.5	
	Flexible c/w lug conductor section			
min	mm ²	0.75		
max	mm ²	2.5		
Flexible with insulated spade lug conductor section				
min	mm ²	0.75		
max	mm ²	2.5		
Mechanical features				
Operating position	normal		On vertical plane	
	allowable		Any	
Fixing			Front centre mounting	
Weight			g	28
Terminals screw			Screw	
Conductor section	AWG/kcmil conductor section			
		max	12	
	IEC			
	max	mm ²	1 or 2 x 2.5	
Auxiliary contact characteristics				
Type of contact				4NO
Thermal current I_{th}	A			10
IEC/EN 60947-5-1 designation				A600 - Q600

Operating current AC15

230V	A	3
400V	A	1.9
500V	A	1.4

Operating current DC13

24V	A	3
48V	A	1.5
60V	A	1.2
110V	A	0.6
125V	A	0.55
220V	A	0.27
600V	A	0.1

Electrical characteristics

Conductivity	5V 10 mA
UL/CSA and IEC/EN 60947-5-1 designation	A600 Q600

Operating current AC15

120V	A	6
240V	A	3
480V	A	1.5
600V	A	1.2

Operating current DC13

12V	A	10
250V	A	0.27
440V	A	0.15
500V	A	0.13

Ambient conditions

Temperature

Operating temperature

min	°C	-50
max	°C	+70


Storage temperature

min	°C	-60
max	°C	+80


Max altitude

m 3000

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 60947-1

CSA C22.2 n° 60947-5-1

IEC/EN 60947-1

IEC/EN 60947-5-1

UL 60947-1

UL 60947-5-1

Certificates

CCC

cULus

EAC

ETIM classification

ETIM 8.0

EC000041 -
Auxiliary contact
block