



| | | | | |
|--|---|----|------|-----------------|
| Product designation | | | | Power contactor |
| Product type designation | | | | BF25 |
| Contact characteristics | | | | |
| Number of poles | Nr. | | | 3 |
| Rated insulation voltage U_i IEC/EN | V | | | 690 |
| Rated impulse withstand voltage U_{imp} | kV | | | 6 |
| Operational frequency | min | Hz | 25 | |
| | max | Hz | 400 | |
| IEC Conventional free air thermal current I_{th} | A | | | 32 |
| Operational current I_e | AC-1 ($\leq 40^\circ\text{C}$) | A | 32 | |
| | AC-1 ($\leq 55^\circ\text{C}$) | A | 26 | |
| | AC-1 ($\leq 70^\circ\text{C}$) | A | 23 | |
| | AC-3 ($\leq 440\text{V} \leq 55^\circ\text{C}$) | A | 25 | |
| | AC-4 (400V) | A | 10 | |
| Rated operational power AC-3 ($T \leq 55^\circ\text{C}$) | 230V | kW | 7 | |
| | 400V | kW | 12.5 | |
| | 415V | kW | 13.4 | |
| | 440V | kW | 13.4 | |
| | 500V | kW | 15 | |
| | 690V | kW | 11 | |
| Rated operational power AC-1 ($T \leq 40^\circ\text{C}$) | 230V | kW | 12 | |
| | 400V | kW | 21 | |
| | 500V | kW | 26 | |
| | 690V | kW | 36 | |
| IEC max current I_e in DC1 with $L/R \leq 1\text{ms}$ with 1 poles in series | $\leq 24\text{V}$ | A | 20 | |
| | 48V | A | 18 | |
| | 75V | A | 18 | |
| | 110V | A | 6 | |
| | 220V | A | - | |
| IEC max current I_e in DC1 with $L/R \leq 1\text{ms}$ with 2 poles in series | $\leq 24\text{V}$ | A | 23 | |
| | 48V | A | 23 | |
| | 75V | A | 23 | |
| | 110V | A | 16 | |
| | 220V | A | 1 | |
| IEC max current I_e in DC1 with $L/R \leq 1\text{ms}$ with 3 poles in series | $\leq 24\text{V}$ | A | 23 | |
| | 48V | A | 23 | |
| | 75V | A | 23 | |
| | 110V | A | 18 | |

| | | | |
|---|-----------------|------------------|-----|
| | 220V | A | 12 |
| IEC max current I_e in DC1 with $L/R \leq 1$ ms with 4 poles in series | | | |
| | ≤ 24 V | A | – |
| | 48V | A | – |
| | 75V | A | – |
| | 110V | A | – |
| | 220V | A | – |
| IEC max current I_e in DC3-DC5 with $L/R \leq 15$ ms with 1 poles in series | | | |
| | ≤ 24 V | A | 15 |
| | 48V | A | 13 |
| | 75V | A | 13 |
| | 110V | A | 2 |
| | 220V | A | – |
| IEC max current I_e in DC3-DC5 with $L/R \leq 15$ ms with 2 poles in series | | | |
| | ≤ 24 V | A | 18 |
| | 48V | A | 18 |
| | 75V | A | 16 |
| | 110V | A | 10 |
| | 220V | A | 2 |
| IEC max current I_e in DC3-DC5 with $L/R \leq 15$ ms with 3 poles in series | | | |
| | ≤ 24 V | A | 22 |
| | 48V | A | 22 |
| | 75V | A | 18 |
| | 110V | A | 15 |
| | 220V | A | 8 |
| IEC max current I_e in DC3-DC5 with $L/R \leq 15$ ms with 4 poles in series | | | |
| | ≤ 24 V | A | – |
| | 48V | A | – |
| | 75V | A | – |
| | 110V | A | – |
| | 220V | A | – |
| Short-time allowable current for 10s (IEC/EN60947-1) | | A | 200 |
| Protection fuse | | | |
| | gG (IEC) | A | 50 |
| | aM (IEC) | A | 25 |
| Making capacity (RMS value) | | A | 250 |
| Breaking capacity at voltage | | | |
| | 440V | A | 200 |
| | 500V | A | 184 |
| | 690V | A | 102 |
| Resistance per pole (average value) | | m Ω | 2.5 |
| Power dissipation per pole (average value) | | | |
| | I _{th} | W | 2.6 |
| | AC-3 | W | 1.6 |
| Tightening torque for terminals | | | |
| | min | Nm | 1.5 |
| | max | Nm | 1.8 |
| | min | I _{bin} | 1.1 |
| | max | I _{bin} | 1.5 |
| Tightening torque for coil terminal | | | |
| | min | Nm | 0.8 |
| | max | Nm | 1 |
| | min | I _{bin} | 0.8 |

| | | | | |
|---|-----------|-----|------------------|--------------------------|
| | | max | I _{bin} | 0.74 |
| Max number of wires simultaneously connectable | | | Nr. | 2 |
| Conductor section | AWG/Kcmil | | | |
| | | max | | 10 |
| Flexible w/o lug conductor section | | min | mm ² | 1 |
| | | max | mm ² | 6 |
| Flexible c/w lug conductor section | | min | mm ² | 1 |
| | | max | mm ² | 4 |
| Flexible with insulated spade lug conductor section | | min | mm ² | 1 |
| | | max | mm ² | 4 |
| Power terminal protection according to IEC/EN 60529 | | | | IP20 when properly wired |

Mechanical features

| | | | | |
|--------------------|-----------------------------|------------------|---|-----------------------|
| Operating position | | normal allowable | | Vertical plan ±30° |
| Fixing | | | | Screw / DIN rail 35mm |
| Weight | | | g | 493 |
| Conductor section | AWG/kcmil conductor section | | | |
| | | max | | 10 |

Auxiliary contact characteristics

| | | | | |
|---------------------------------|--|------|---|-------------|
| Thermal current I _{th} | | A | | 10 |
| IEC/EN 60947-5-1 designation | | | | A600 - P600 |
| Operating current AC15 | | 230V | A | 3 |
| | | 400V | A | 1.9 |
| | | 500V | A | 1.4 |
| Operating current DC12 | | 110V | A | 5.7 |
| Operating current DC13 | | 24V | A | 5.7 |
| | | 48V | A | 2.9 |
| | | 60V | A | 2.3 |
| | | 110V | A | 1.25 |
| | | 125V | A | 1.1 |
| | | 220V | A | 0.55 |
| | | 600V | A | 0.2 |

Operations

| | | | | |
|-----------------|--|--------|--|----------|
| Mechanical life | | cycles | | 20000000 |
| Electrical life | | cycles | | 1200000 |

Safety related data

| | | | | |
|--|--|-----------------|--------|----------|
| Performance level B10d according to EN/ISO 13489-1 | | rated load | cycles | 1200000 |
| | | mechanical load | cycles | 20000000 |
| Mirror contacts according to IEC/EN 60947-4-1 | | | | yes |
| EMC compatibility | | | | yes |

DC coil operating

| | | | |
|--|----------|-----|---------|
| DC rated control voltage | | V | 125 |
| DC operating voltage | | | |
| | pick-up | min | %Us 70 |
| | | max | %Us 125 |
| | drop-out | min | %Us 10 |
| | | max | %Us 40 |
| Average coil consumption $\leq 20^{\circ}\text{C}$ | | | |
| | in-rush | W | 5.4 |
| | holding | W | 5.4 |

Max cycles frequency

| | | | |
|----------------------|--|----------|------|
| Mechanical operation | | cycles/h | 3600 |
|----------------------|--|----------|------|

Operating times

| | | | |
|-----------------------------|------------|-----|-------|
| Average time for Us control | | | |
| | in AC | | |
| | Closing NO | min | ms 8 |
| | | max | ms 24 |
| | Opening NO | min | ms 10 |
| | | max | ms 20 |
| | Closing NC | min | ms 14 |
| | | max | ms 28 |
| | Opening NC | min | ms 7 |
| | | max | ms 18 |
| | in DC | | |
| | Closing NO | min | ms 54 |
| | | max | ms 66 |
| | Opening NO | min | ms 14 |
| | | max | ms 17 |
| | Closing NC | min | ms 24 |
| | | max | ms 30 |
| | Opening NC | min | ms 47 |
| | | max | ms 57 |

UL technical data

| | | | |
|--|---------|---|----|
| Full-load current (FLA) for three-phase AC motor | | | |
| | at 480V | A | 21 |
| | at 600V | A | 17 |

| | | | |
|--------------------------------|---------------------------|----|-----|
| Yielded mechanical performance | | | |
| | for single-phase AC motor | | |
| | 110/120V | HP | 2 |
| | 230V | HP | 3 |
| | for three-phase AC motor | | |
| | 200/208V | HP | 7.5 |
| | 220/230V | HP | 7.5 |
| | 460/480V | HP | 15 |
| | 575/600V | HP | 15 |

General USE

| | | | |
|--------------------|------------|---|-----|
| Contactor | AC current | A | 32 |
| Auxiliary contacts | AC voltage | V | 600 |
| | AC current | A | 10 |
| | DC voltage | V | 250 |
| | DC current | A | 1 |

Short-circuit protection fuse, 600V

| | | | |
|----------------|-----------------------|----|-----|
| High fault | Short circuit current | kA | 100 |
| | Fuse rating | A | 60 |
| | Fuse class | | J |
| Standard fault | Short circuit current | kA | 5 |
| | Fuse rating | A | 100 |

Contact rating of auxiliary contacts according to UL

A600 - P600

Ambient conditions

Temperature

| | | | |
|-----------------------|-----|----|-----|
| Operating temperature | min | °C | -50 |
| | max | °C | 70 |
| Storage temperature | min | °C | -60 |
| | max | °C | 80 |

Max altitude

m 3000

Resistance & Protection

Pollution degree

3

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

- CSA C22.2 n° 60947-1
- CSA C22.2 n° 60947-4-1
- IEC/EN/BS 60947-1
- IEC/EN/BS 60947-4-1
- UL 60947-1
- UL 60947-4-1

Certificates

CCC

cULus

EAC

ETIM classification

ETIM 8.0

EC000066 -
Power contactor,
AC switching