



Product designation			Power contactor
Product type designation			BF630
Contact characteristics			
Number of poles	Nr.	3	
Rated insulation voltage Ui IEC/EN	V	1000	
Rated impulse withstand voltage Uimp	kV	8	
Operational frequency	min	Hz	25
	max	Hz	400
IEC Conventional free air thermal current Ith	A	800	
Operational current Ie	AC-1 (≤40°C)	A	800
	AC-1 (≤55°C)	A	660
	AC-1 (≤70°C)	A	570
	AC-3 (≤440V ≤55°C)	A	630
	AC-4 (400V)	A	260
Rated operational power AC-3 (T≤55°C)	230V	kW	200
	400V	kW	355
	415V	kW	355
	440V	kW	400
	500V	kW	400
	690V	kW	500
	1000V	kW	250
Rated operational current AC-3 (T≤55°C)	230V	A	630
	400V	A	630
	415V	A	630
	440V	A	630
	500V	A	552
	690V	A	493
	1000V	A	250
Rated operational power AC-1 (T≤40°C)	230V	kW	303
	400V	kW	527
	500V	kW	579
	690V	kW	908
IEC max current Ie in DC1 with L/R ≤ 1ms with 1 poles in series	75V	A	800
	110V	A	460
IEC max current Ie in DC1 with L/R ≤ 1ms with 2 poles in series	75V	A	800
	110V	A	800
	220V	A	700
IEC max current Ie in DC1 with L/R ≤ 1ms with 3 poles in series			

	75V	A	800
	110V	A	800
	220V	A	800
	330V	A	700
IEC max current Ie in DC1 with L/R ≤ 1ms with 4 poles in series			
	75V	A	800
	110V	A	800
	220V	A	800
IEC max current Ie in DC3-DC5 with L/R ≤ 15ms with 1 poles in series			
	75V	A	800
	110V	A	460
IEC max current Ie in DC3-DC5 with L/R ≤ 15ms with 2 poles in series			
	75V	A	800
	110V	A	800
	220V	A	700
IEC max current Ie in DC3-DC5 with L/R ≤ 15ms with 3 poles in series			
	75V	A	800
	110V	A	800
	220V	A	800
	330V	A	650
IEC max current Ie in DC3-DC5 with L/R ≤ 15ms with 4 poles in series			
	75V	A	800
	110V	A	800
	220V	A	800
	330V	A	700
	460V	A	700
Short-time allowable current for 10s (IEC/EN60947-1)		A	5040
Protection fuse			
	gG (IEC)	A	1000
	aM (IEC)	A	630
Making capacity (RMS value)		A	6300
Breaking capacity at voltage			
	440V	A	6300
	500V	A	4416
	690V	A	3944
Resistance per pole (average value)		mΩ	0.09
Power dissipation per pole (average value)			
	Ith	W	64
	AC-3	W	40
Tightening torque for terminals			
	min	Nm	55
	max	Nm	55
	min	Ibin	486
	max	Ibin	486
Tightening torque for coil terminal			
	min	Nm	0.8
	max	Nm	1
	min	Ibin	7.1
	max	Ibin	8.8
Power terminal protection according to IEC/EN 60529			IP00

Mechanical features

Operating position

normal

Vertical plan

		allowable	±30°	
Fixing		Screw		
Operations				
Mechanical life		cycles	5000000	
Electrical life		cycles	600000	
Safety related data				
Performance level B10d according to EN/ISO 13489-1				
		rated load	cycles	600000
		mechanical load	cycles	5000000
EMC compatibility				
yes				
AC coil operating				
Rated AC voltage at 50/60Hz, 60Hz				
		min	V	250
		max	V	500
AC operating voltage				
of 50/60Hz coil powered at 50Hz				
pick-up		min	%Us	80 Us min
		max	%Us	110 Us max
drop-out		max	%Us	≤70 Us min
of 50/60Hz coil powered at 60Hz				
pick-up		min	%Us	80 Us min
		max	%Us	110 Us max
drop-out		max	%Us	≤70 Us min
AC average coil consumption at 20°C				
of 50/60Hz coil powered at 50Hz		in-rush	VA	390
		holding	VA	12
of 50/60Hz coil powered at 60Hz				
		in-rush	VA	390
		holding	VA	12
Dissipation at holding ≤20°C 50Hz			W	4
DC coil operating				
DC rated control voltage				
		min	V	250
		max	V	500
DC operating voltage				
pick-up		min	%Us	85 Us min
		max	%Us	110 Us max
drop-out		max	%Us	≤70 Us min
Average coil consumption ≤20°C				
		in-rush	W	390
		holding	W	4
Max cycles frequency				
Mechanical operation		cycles/h	1000	
Operating times				
Average time for Us control				
in AC				

Closing NO

min	ms	95
max	ms	135

Opening NO

min	ms	40
max	ms	53

UL technical data

Rated operational voltage AC (UL)	V	600
-----------------------------------	---	-----

Yielded mechanical performance

for three-phase AC motor

200/208V	HP	200
220/240V	HP	250
460/480V	HP	500
575/600V	HP	600

General USE

Contactor

AC current	A	800
------------	---	-----

Short-circuit protection fuse, 600V

High fault

Short circuit current	kA	100
Fuse rating	A	800
Fuse class		L

Standard fault

Short circuit current	kA	30
Fuse rating	A	1000
Fuse class		L

Ambient conditions

Temperature

Operating temperature

min	°C	-40
max	°C	70

Storage temperature

min	°C	-50
max	°C	80

Max altitude


m	3000
---	------

Resistance & Protection


Pollution degree

3

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 60947-1

CSA C22.2 n° 60947-4-1

IEC/EN/BS 60947-1

IEC/EN/BS 60947-4-1

UL 60947-1

UL 60947-4-1

Certificates

cULus

ETIM classification

ETIM 8.0

EC000066 -
Power contactor,
AC switching