



Product designation Power contactor
Product type designation BF94

Contact characteristics

| | | |
|--|---|--------|
| Number of poles | Nr. | 3 |
| Rated insulation voltage U_i IEC/EN | V | 1000 |
| Rated impulse withstand voltage U_{imp} | kV | 8 |
| Operational frequency | min | Hz 25 |
| | max | Hz 400 |
| IEC Conventional free air thermal current I_{th} | A | 115 |
| Operational current I_e | AC-1 ($\leq 40^\circ\text{C}$) | A 115 |
| | AC-1 ($\leq 55^\circ\text{C}$) | A 95 |
| | AC-1 ($\leq 70^\circ\text{C}$) | A 80 |
| | AC-3 ($\leq 440\text{V} \leq 55^\circ\text{C}$) | A 95 |
| | AC-4 (400V) | A 45 |
| Rated operational power AC-3 ($T \leq 55^\circ\text{C}$) | 230V | kW 30 |
| | 400V | kW 55 |
| | 415V | kW 55 |
| | 440V | kW 55 |
| | 500V | kW 55 |
| | 690V | kW 55 |
| | 1000V | kW 37 |
| Rated operational current AC-3 ($T \leq 55^\circ\text{C}$) | 230V | A 94 |
| | 400V | A 94 |
| | 415V | A 94 |
| | 440V | A 94 |
| | 500V | A 78 |
| | 690V | A 57 |
| | 1000V | A 28 |
| IEC max current I_e in DC1 with $L/R \leq 1\text{ms}$ with 1 poles in series | $\leq 24\text{V}$ | A 77 |
| | 48V | A 66 |
| | 75V | A 66 |
| | 110V | A 8 |
| | 220V | A – |
| IEC max current I_e in DC1 with $L/R \leq 1\text{ms}$ with 2 poles in series | $\leq 24\text{V}$ | A 110 |
| | 48V | A 110 |
| | 75V | A 110 |
| | 110V | A 90 |
| | 220V | A 9 |
| IEC max current I_e in DC1 with $L/R \leq 1\text{ms}$ with 3 poles in series | | |

| | | | |
|--|-----------------|------------------|-----|
| | ≤24V | A | 110 |
| | 48V | A | 110 |
| | 75V | A | 110 |
| | 110V | A | 93 |
| | 220V | A | 95 |
| <hr/> | | | |
| IEC max current I _e in DC1 with L/R ≤ 1ms with 4 poles in series | ≤24V | A | 115 |
| | 48V | A | 115 |
| | 75V | A | 115 |
| | 110V | A | 110 |
| | 220V | A | 115 |
| <hr/> | | | |
| IEC max current I _e in DC3-DC5 with L/R ≤ 15ms with 1 poles in series | ≤24V | A | 45 |
| | 48V | A | 33 |
| | 75V | A | 33 |
| | 110V | A | 3 |
| | 220V | A | – |
| <hr/> | | | |
| IEC max current I _e in DC3-DC5 with L/R ≤ 15ms with 2 poles in series | ≤24V | A | 65 |
| | 48V | A | 55 |
| | 75V | A | 55 |
| | 110V | A | 43 |
| | 220V | A | 5 |
| <hr/> | | | |
| IEC max current I _e in DC3-DC5 with L/R ≤ 15ms with 3 poles in series | ≤24V | A | 86 |
| | 48V | A | 75 |
| | 75V | A | 75 |
| | 110V | A | 64 |
| | 220V | A | 64 |
| <hr/> | | | |
| IEC max current I _e in DC3-DC5 with L/R ≤ 15ms with 4 poles in series | ≤24V | A | 96 |
| | 48V | A | 95 |
| | 75V | A | 95 |
| | 110V | A | 80 |
| | 220V | A | 80 |
| <hr/> | | | |
| Short-time allowable current for 10s (IEC/EN60947-1) | | A | 640 |
| <hr/> | | | |
| Protection fuse | gG (IEC) | A | 125 |
| | aM (IEC) | A | 100 |
| <hr/> | | | |
| Making capacity (RMS value) | | A | 950 |
| <hr/> | | | |
| Breaking capacity at voltage | 440V | A | 640 |
| | 500V | A | 625 |
| | 690V | A | 456 |
| <hr/> | | | |
| Resistance per pole (average value) | | mΩ | 0.6 |
| <hr/> | | | |
| Power dissipation per pole (average value) | I _{th} | W | 7.9 |
| | AC-3 | W | 5.4 |
| <hr/> | | | |
| Tightening torque for terminals | min | Nm | 4 |
| | max | Nm | 5 |
| | min | I _{bin} | 3 |
| | max | I _{bin} | 3.7 |

Tightening torque for coil terminal

| | | |
|-----|------|------|
| min | Nm | 0.8 |
| max | Nm | 1 |
| min | Ibin | 0.59 |
| max | Ibin | 0.74 |

Max number of wires simultaneously connectable

Nr. 2

Conductor section

Flexible w/o lug conductor section

| | | |
|-----|-----------------|-----|
| min | mm ² | 1.5 |
| max | mm ² | 35 |

Power terminal protection according to IEC/EN 60529

IP20

Mechanical features

Operating position

normal allowable Vertical plan
±30°

Fixing

Screw / DIN rail
35mm

Weight

g 1

Operations

Mechanical life

cycles 15000000

Electrical life

cycles 1100000

Safety related data

Mirror contacts according to IEC/EN 609474-4-1

YES

EMC compatibility

yes

AC coil operating

Rated AC voltage at 50/60Hz

V 48

AC operating voltage

of 50/60Hz coil powered at 50Hz
pick-up

| | | |
|-----|-----|-----|
| min | %Us | 80 |
| max | %Us | 110 |

drop-out

| | | |
|-----|-----|----|
| min | %Us | 20 |
| max | %Us | 55 |

of 50/60Hz coil powered at 60Hz
pick-up

| | | |
|-----|-----|-----|
| min | %Us | 85 |
| max | %Us | 110 |

drop-out

| | | |
|-----|-----|----|
| min | %Us | 20 |
| max | %Us | 55 |

of 60Hz coil powered at 60Hz
pick-up

| | | |
|-----|-----|-----|
| min | %Us | 80 |
| max | %Us | 110 |

drop-out

| | | |
|-----|-----|----|
| min | %Us | 20 |
| max | %Us | 55 |

AC average coil consumption at 20°C

of 50/60Hz coil powered at 50Hz


| | | |
|---------|----|-----|
| in-rush | VA | 210 |
| holding | VA | 15 |

of 50/60Hz coil powered at 60Hz


| | | |
|---------|----|-----|
| in-rush | VA | 195 |
|---------|----|-----|

| | | | |
|--|-----------------------|----------|-------|
| | holding | VA | 13 |
| of 60Hz coil powered at 60Hz | | | |
| | in-rush | VA | 210 |
| | holding | VA | 15 |
| Dissipation at holding ≤20°C 50Hz | | W | 5 |
| Max cycles frequency | | | |
| Mechanical operation | | cycles/h | 3600 |
| Operating times | | | |
| Average time for Us control | | | |
| in AC | | | |
| | Closing NO | min | ms 12 |
| | | max | ms 28 |
| | Opening NO | min | ms 8 |
| | | max | ms 22 |
| in DC | | | |
| | Closing NO | min | ms 40 |
| | | max | ms 85 |
| | Opening NO | min | ms 20 |
| | | max | ms 55 |
| UL technical data | | | |
| Full-load current (FLA) for three-phase AC motor | | | |
| | at 480V | A | 77 |
| | at 600V | A | 77 |
| Yielded mechanical performance | | | |
| for three-phase AC motor | | | |
| | 200/208V | HP | 25 |
| | 220/230V | HP | 30 |
| | 460/480V | HP | 60 |
| | 575/600V | HP | 75 |
| General USE | | | |
| Contactor | | | |
| | AC current | A | 115 |
| Short-circuit protection fuse, 600V | | | |
| High fault | | | |
| | Short circuit current | kA | 100 |
| | Fuse rating | A | 200 |
| | Fuse class | | J |
| Standard fault | | | |
| | Short circuit current | kA | 10 |
| | Fuse rating | A | 200 |
| | Fuse class | | RK5 |
| Ambient conditions | | | |
| Temperature | | | |
| Operating temperature | | | |
| | min | °C | -50 |
| | max | °C | 70 |
| Storage temperature | | | |
| | min | °C | -60 |
| | max | °C | 80 |
| Max altitude | | m | 3000 |

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

- CSA C22.2 n° 60947-1
- CSA C22.2 n° 60947-4-1
- IEC/EN/BS 60947-1
- IEC/EN/BS 60947-4-1
- UL 60947-1
- UL 60947-4-1

Certificates

CCC

cULus

EAC

ETIM classification

ETIM 8.0

EC000066 -
Power contactor,
AC switching