



Product designation Power contactor  
Product type designation BFK115

**Contact characteristics**

Number of poles	Nr.	3
Rated insulation voltage $U_i$ IEC/EN	V	690
Rated impulse withstand voltage $U_{imp}$	kV	8
Operational frequency	min	Hz 25
	max	Hz 400
IEC Conventional free air thermal current $I_{th}$	A	160
Rated operational power AC-6b ( $T \leq 40^\circ C$ )	230V	kvar 45
	400V	kvar 75
	440...480V	kvar 85
	690V	kvar 135
Short-time allowable current for 10s (IEC/EN60947-1)	A	920
Protection fuse	gG (IEC)	A 160
		A 1500
Making capacity (RMS value)	A	1500
Breaking capacity at voltage	440V	A 1200
	500V	A 850
	690V	A 905
Resistance per pole (average value)	m $\Omega$	0.45
Power dissipation per pole (average value)	$I_{th}$	W 11.5
Tightening torque for terminals	min	Nm 6
	max	Nm 7
	min	lbin 4.4
	max	lbin 5.2
Tightening torque for coil terminal	min	Nm 0.8
	max	Nm 1
	min	lbin 0.59
	max	lbin 0.74
Max number of wires simultaneously connectable	Nr.	2
Conductor section	AWG/Kcmil	
	max	2/0
Flexible w/o lug conductor section	min	mm <sup>2</sup> 1.5
	max	mm <sup>2</sup> 70
Flexible c/w lug conductor section	min	mm <sup>2</sup> 1.5


		max	mm <sup>2</sup>	70
Power terminal protection according to IEC/EN 60529				IP20 front
<b>Mechanical features</b>				
Operating position		normal allowable		Vertical plan ±30°
Fixing				Screw / DIN rail 35mm
Weight			g	2095
Conductor section	AWG/kcmil conductor section	max		2/0
<b>Operations</b>				
Mechanical life			cycles	15000000
Electrical life			cycles	1200000
<b>Safety related data</b>				
Performance level B10d according to EN/ISO 13489-1		rated load mechanical load	cycles cycles	400000 15000000
EMC compatibility				yes
<b>AC coil operating</b>				
Rated AC voltage at 60Hz			V	575
AC operating voltage	of 60Hz coil powered at 60Hz			
	pick-up	min	%Us	80
		max	%Us	110
	drop-out	min	%Us	20
		max	%Us	55
<b>Max cycles frequency</b>				
Mechanical operation			cycles/h	1500
<b>Operating times</b>				
Average time for Us control in AC	Closing NO	min	ms	16
		max	ms	32
	Opening NO	min	ms	9
		max	ms	24
<b>UL technical data</b>				
General USE	Contactor	AC current	A	160
<b>Ambient conditions</b>				
Temperature	Operating temperature	min	°C	-50
		max	°C	70
	Storage temperature	min	°C	-60
		max	°C	80
Max altitude			m	3000

Resistance & Protection


Pollution degree

3

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 60947-1

CSA C22.2 n° 60947-4-1

IEC/EN/BS 60947-1

IEC/EN/BS 60947-4-1

UL 60947-1

UL 60947-4-1

Certificates

CCC

cULus

ETIM classification

ETIM 8.0

EC001079 -  
Capacitor  
contactor