



| | | | | |
|---|------------|-----------------|------|-----------------|
| Product designation | | | | Power contactor |
| Product type designation | | | | BFK115 |
| Contact characteristics | | | | |
| Number of poles | Nr. | | | 3 |
| Rated insulation voltage U_i IEC/EN | V | | | 690 |
| Rated impulse withstand voltage U_{imp} | kV | | | 8 |
| Operational frequency | min | Hz | 25 | |
| | max | Hz | 400 | |
| IEC Conventional free air thermal current I_{th} | A | | | 160 |
| Rated operational power AC-6b ($T \leq 40^\circ C$) | 230V | kvar | 45 | |
| | 400V | kvar | 75 | |
| | 440...480V | kvar | 85 | |
| | 690V | kvar | 135 | |
| Short-time allowable current for 10s (IEC/EN60947-1) | A | | | 920 |
| Protection fuse | gG (IEC) | A | 160 | |
| | | A | 1500 | |
| Making capacity (RMS value) | | | | 1500 |
| Breaking capacity at voltage | 440V | A | 1200 | |
| | 500V | A | 850 | |
| | 690V | A | 905 | |
| | | m Ω | 0.45 | |
| Resistance per pole (average value) | | | | 0.45 |
| Power dissipation per pole (average value) | I_{th} | W | 11.5 | |
| | | | | |
| Tightening torque for terminals | min | Nm | 6 | |
| | max | Nm | 7 | |
| | min | Ibin | 4.4 | |
| | max | Ibin | 5.2 | |
| Tightening torque for coil terminal | min | Nm | 0.8 | |
| | max | Nm | 1 | |
| | min | Ibin | 0.59 | |
| | max | Ibin | 0.74 | |
| Max number of wires simultaneously connectable | Nr. | | | 2 |
| Conductor section | AWG/Kcmil | | | |
| | max | | | 2/0 |
| Flexible w/o lug conductor section | min | mm ² | 1.5 | |
| | max | mm ² | 70 | |
| Flexible c/w lug conductor section | min | mm ² | 1.5 | |

| | | | | |
|---|---------------------------------|----------------------------|-----------------|-----------------------|
| | | max | mm ² | 70 |
| Power terminal protection according to IEC/EN 60529 | | | | IP20 front |
| Mechanical features | | | | |
| Operating position | | normal allowable | | Vertical plan ±30° |
| Fixing | | | | Screw / DIN rail 35mm |
| Weight | | | g | 2095 |
| Conductor section | AWG/kcmil conductor section | max | | 2/0 |
| Operations | | | | |
| Mechanical life | | | cycles | 15000000 |
| Electrical life | | | cycles | 1200000 |
| Safety related data | | | | |
| Performance level B10d according to EN/ISO 13489-1 | | rated load mechanical load | cycles cycles | 400000 15000000 |
| EMC compatibility | | | | yes |
| AC coil operating | | | | |
| Rated AC voltage at 50/60Hz | | | V | 400 |
| AC operating voltage | of 50/60Hz coil powered at 50Hz | | | |
| | pick-up | min | %Us | 80 |
| | | max | %Us | 110 |
| | drop-out | min | %Us | 20 |
| | | max | %Us | 55 |
| | of 50/60Hz coil powered at 60Hz | | | |
| | pick-up | min | %Us | 85 |
| | | max | %Us | 110 |
| | drop-out | min | %Us | 40 |
| | | max | %Us | 55 |
| AC average coil consumption at 20°C | of 50/60Hz coil powered at 50Hz | holding | VA | 20 |
| | of 50/60Hz coil powered at 60Hz | in-rush | VA | 300 |
| | | holding | VA | 17 |
| | of 60Hz coil powered at 60Hz | in-rush | VA | 300 |
| | | holding | VA | 20 |
| Dissipation at holding ≤20°C 50Hz | | | W | 6.5 |
| Max cycles frequency | | | | |
| Mechanical operation | | | cycles/h | 1500 |
| Operating times | | | | |
| Average time for Us control in AC | Closing NO | min | ms | 16 |

| | | | |
|------------|-----|----|----|
| Opening NO | max | ms | 32 |
| | min | ms | 9 |
| | max | ms | 24 |

UL technical data

General USE

Contactor

AC current A 160

Ambient conditions

Temperature

Operating temperature

min °C -50
max °C 70

Storage temperature

min °C -60
max °C 80

Max altitude


m 3000

Resistance & Protection


Pollution degree

3

Dimensions



Wiring diagrams



Ⓜ Auxiliary contact 13-14 is found on BFK09 A - BFK12 A - BFK18 A types only.

Certifications and compliance

Compliance

CSA C22.2 n° 60947-1

CSA C22.2 n° 60947-4-1

IEC/EN/BS 60947-1

IEC/EN/BS 60947-4-1

UL 60947-1

UL 60947-4-1

Certificates

CCC

cULus

ETIM classification

ETIM 8.0

EC001079 -
Capacitor
contactor