



Product designation				Auxiliary contact
Product type designation				BFX12
Contact characteristics				
Number of poles	Nr.	2		
Rated insulation voltage U_i IEC/EN	V	690		
Rated impulse withstand voltage U_{imp}	kV	6		
IEC Conventional free air thermal current I_{th}	A	10		
Tightening torque for terminals	min	Nm	0.8	
	max	Nm	1	
	min	lbin	7	
	max	lbin	9	
Max number of wires simultaneously connectable	Nr.	2		
Conductor section	AWG/Kcmil			
		max	14	
	Flexible w/o lug conductor section			
		min	mm ²	0.75
		max	mm ²	2.5
	Flexible c/w lug conductor section			
		min	mm ²	0.75
		max	mm ²	2.5
Flexible with insulated spade lug conductor section				
	min	mm ²	0.75	
	max	mm ²	2.5	
Mechanical features				
Operating position	normal		On vertical plane	
	allowable		Any	
Fixing				Side mounting
Weight				g 44
Terminals screw				Screw
Conductor section	AWG/kcmil conductor section			
		max	14	
	IEC			
		max	mm ²	1 or 2 x 2.5
Auxiliary contact characteristics				
Type of contact				1NO+1NC
Thermal current I_{th}	A	10		
IEC/EN 60947-5-1 designation				A600 - Q600
Operating current AC15	230V	A	3	
	400V	A	1.9	
	500V	A	1.4	

Operating current DC13

24V	A	3
48V	A	1.5
60V	A	1.2
110V	A	0.6
125V	A	0.55
220V	A	0.27
600V	A	0.1

Electrical characteristics

Conductivity	5V 10 mA
UL/CSA and IEC/EN 60947-5-1 designation	A600 Q600

Operating current AC15

120V	A	6
240V	A	3
480V	A	1.5
600V	A	1.2

Operating current DC13

12V	A	10
250V	A	0.27
440V	A	0.15
500V	A	0.13

AC coil operating

AC operating voltage

of 50/60Hz coil powered at 50Hz
pick-up

min	%Us	"
max	%Us	"

Ambient conditions

Temperature

Operating temperature

min	°C	-50
max	°C	+70


Storage temperature

min	°C	-60
max	°C	+80


Max altitude

m	3000
---	------

Dimensions



Wiring diagrams



Certifications and compliance

Compliance

- CSA C22.2 n° 60947-1

- CSA C22.2 n° 60947-5-1

- IEC/EN 60947-1

- IEC/EN 60947-5-1

- UL 60947-1

- UL 60947-5-1

Certificates

- CCC

- cULus

- EAC

ETIM classification

ETIM 8.0

EC000041 -
 Auxiliary contact
 block