



3P Insulated parallel link for BF40...BF94 BFX3399

Product designation

Product type designation

Contact characteristics

Rated insulation voltage U_i IEC/EN V 1000

Tightening torque for terminals

max	Nm	13
max	lbin	115

Conductor section

Flexible w/o lug conductor section

min	mm ²	25
max	mm ²	95

Mechanical features

Weight g 135

Auxiliary contact characteristics

Thermal current I_{th} A 200

Certifications and compliance

Certificates

/

ETIM classification

ETIM 8.0

EC002498 - Accessories/spare parts for low-voltage switch technology