



AC coil operating

Rated AC voltage at 50/60Hz, 60Hz

min	V	60
max	V	110

AC operating voltage

of 50/60Hz coil powered at 50Hz
pick-up

min	%Us	80 Us min
max	%Us	110 Us max

drop-out

max	%Us	≤70 Us min
-----	-----	------------

of 50/60Hz coil powered at 60Hz
pick-up

min	%Us	80 Us min
max	%Us	110 Us max

drop-out

max	%Us	≤70 Us min
-----	-----	------------

AC average coil consumption at 20°C

of 50/60Hz coil powered at 50Hz

in-rush	VA	70...175
holding	VA	1.7...3.5

of 50/60Hz coil powered at 60Hz

in-rush	VA	70...175
holding	VA	1.7...3.5

of 60Hz coil powered at 60Hz

in-rush	VA	70...175
holding	VA	1.7...3.5

Dissipation at holding ≤20°C 50Hz

W	1.3...1.5
---	-----------

Certifications and compliance

Certificates

/

ETIM classification

ETIM 8.0

EC002563 - Coil
for low-voltage