



AC coil operating

Rated AC voltage at 50/60Hz V 24

AC operating voltage

| | | | | |
|---------------------------------|-----|-----|--|-----|
| of 50/60Hz coil powered at 50Hz | | | | |
| pick-up | | | | |
| | min | %Us | | 80 |
| | max | %Us | | 110 |
| drop-out | | | | |
| | min | %Us | | 20 |
| | max | %Us | | 55 |

| | | | | |
|---------------------------------|-----|-----|--|-----|
| of 50/60Hz coil powered at 60Hz | | | | |
| pick-up | | | | |
| | min | %Us | | 85 |
| | max | %Us | | 110 |
| drop-out | | | | |
| | min | %Us | | 40 |
| | max | %Us | | 55 |

AC average coil consumption at 20°C

| | | | | |
|---------------------------------|---------|----|--|-----|
| of 50/60Hz coil powered at 50Hz | | | | |
| | in-rush | VA | | 210 |
| | holding | VA | | 15 |

| | | | | |
|---------------------------------|---------|----|--|-----|
| of 50/60Hz coil powered at 60Hz | | | | |
| | in-rush | VA | | 195 |
| | holding | VA | | 13 |

| | | | | |
|------------------------------|---------|----|--|-----|
| of 60Hz coil powered at 60Hz | | | | |
| | in-rush | VA | | 210 |
| | holding | VA | | 15 |

Dissipation at holding ≤20°C 50Hz W 5

Certifications and compliance

Certificates /

ETIM classification

ETIM 8.0 EC002563 - Coil for low-voltage