Lovato electric
ENERGY AND AUTOMATION

DM3T0250

PRZEKŁADNIK PRĄDOWY 250/5A, ŚREDNICA OTWORU 30MM

Wejścia prądowe			
Prąd pierwotny Ipn (/5)		A	250
Częstotliwość robocza			
	min.	Hz	50
	maks.	Hz	60
Prąd strony wtórnej		A	5
Przeciążenie wytrzymywane Ipn		%	120
Obciążenie			
	Kl. obciążenia 1	VA	5
Izolacja			
Znamionowe napięcie izolacji Ui IEC/EN		V	720
Znamionowy prąd termiczny krótkotrwały Ith wg IEC		Ith for s	40…60
Znamionowy prąd dynamiczny Idyn wg IEC		Ith for s	2.5
Typ suchej izolacji			Klasa E
Właściwości mechaniczne			
Typ zacisków			Faston
Montaż			Na szynie DIN lub śrubami
Masa		g	260
Warunki otoczenia			
Temperatura			
Temperatura pracy			
	min.	°C	-25
	maks.	°C	+50
Temperatura składowania			
	min.	°C	-40
	maks.	°C	+80
Wilgotność względna		%	90
Stopień ochrony			IP30
Wymiary			

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding



Certyfikaty i zgodność

Certyfikaty

	IEC/EN/BS 61869-1
	IEC/EN/BS 61869-2

Zgodność

	EAC

Klasyfikacja ETIM

EC000066 - Stycznik mocy, przełączanie AC

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding