



Ref. Certif. No.

DE 3 - 32689

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT  
(IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product

Energy Meters  
Power Analyzer

Name and address of the applicant

**LOVATO ELECTRIC S.p.A.**  
Via Don Emilio Mazza 12  
24020 Gorle (BG)  
ITALY

Name and address of the manufacturer

LOVATO ELECTRIC S.p.A.  
Via Don Emilio Mazza 12, 24020 Gorle (BG), ITALY

Name and address of the factory

LOVATO ELECTRIC S.p.A.  
Via Don Emilio Mazza 12, 24020 Gorle (BG), ITALY

Ratings and principal characteristics

Rated voltage: 100-240 V ac  
Rated frequency: 50/60 Hz  
Rated voltage: 110-250 V dc  
Rated power: 15 VA, 4.0 W

Trademark / Brand (if any)

LOVATO electric

Model/type Ref.

DMG3000, DMG2500, DMG2000

Additional information (if necessary)

Evaluated to National or Group Differences for US, CA, EU Group  
DifferencesA sample of the product was tested and found  
to be in conformity withIEC 61010-1:2010  
IEC 61010-1:2010/AMD1:2016  
IEC 61010-2-030:2023as shown in the Test Report Ref. No.  
which forms part of this certificateELS-V200220011879A-000  
ELS-V200220011879B-000

Page 1 of 1

This CB Test Certificate is issued by the National Certification Body

CB 084111 0062 Rev. 00

Date, 2025-10-14

( Fabrizio Gasparella )

TÜV SÜD Product Service GmbH • Certification Body • Ridlerstraße 65 • 80339 Munich • Germany



Product Service