



Ref. Certif. No.

DE 3 - 31058

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEMESYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC**CB TEST CERTIFICATE**
CERTIFICAT D'ESSAI OC

Product

Name and address of the applicant



Name and address of the manufacturer

Name and address of the factory

Ratings and principal characteristics

Trade mark (if any)

Model/type Ref.

A sample of the product was tested and found
to be in conformity withas shown in the Test Report Ref. No.
which forms part of this certificate

Control units

(Automatic transfer switch)

LOVATO ELECTRIC S.p.A.Via Don Emilio Mazza 12
24020 Gorle (BG)
ITALY

LOVATO ELECTRIC S.p.A.

Via Don Emilio Mazza 12, 24020 Gorle (BG), ITALY

LOVATO ELECTRIC S.p.A.

Via Don Emilio Mazza 12, 24020 Gorle (BG), ITALY

Rated voltage input:

110-240 VAC - LN

Rated input frequency:

190-415 VAC - 3N

Rated input power:

50/60 Hz

2,7 VA - 1,5 W (110 VAC)

3,7 VA - 1,7 W (240 VAC)

Protection class:

II

Measurement category:

III

Degree of protection:

IP40 on front

IP65 on front with gasket

IP20 on terminals

Lovato Electric

ATL500

IEC 61010-1:2010

IEC 61010-2-030:2017

068-ELS1289478C-000

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**

CB 084111 0039 Rev. 00

Date, 2019-09-26

Page 1 of 1

TÜV SÜD Product Service GmbH • Certification Body • Ridlerstraße 65 • 80339 Munich • Germany



Product Service