



Product designation

Direct-on-line
starter

Product type designation

M0P00912...5

Electrical features

Relay adj range		A	3-5
IEC technical characteristics ($\leq 440V$)			
	le	A	5
	kW	kW	1.5...2.2

Components

Starter enclosure standard supplied	M0PA
Contactors standard supplied	BG0910A
Thermal relay standard supplied	RF95

UL technical data

Maximum UL/CSA horsepower ratings single-phase	220V-240V	HP	0.5
Maximum UL/CSA horsepower ratings three-phase, 3-pole	200V-208V	HP	1
	220V-240V	HP	1
	440V-480V	HP	3
	550V-600V	HP	3

Mechanical features

Weight	g	760
--------	---	-----

Ambient conditions

Operating temperature	min	°C	-25
	max	°C	+60
Storage temperature	min	°C	-40
	max	°C	+70

Resistance & Protection

Frontal IP degree	IP65
-------------------	------

ETIM classification

ETIM 8.0	EC001037 - Motor starter/Motor starter combination
----------	--