

Product designation	Direct-on-line starter		
Product type designation	M0P01212...15		
Electrical features			
Relay adj range	A 9-15		
IEC technical characteristics ($\leq 440V$)			
	I _e kW	A kW	12 5.5
Components			
Starter enclosure standard supplied	M0PA		
Contactor standard supplied	BG1210A		
Thermal relay standard supplied	RF915		
UL technical data			
Maximum UL/CSA horsepower ratings single-phase			
	110V-120V	HP	0.5
	220V-240V	HP	1.5
Maximum UL/CSA horsepower ratings three-phase, 3-pole			
	200V-208V	HP	3
	220V-240V	HP	3
	440V-480V	HP	7.5
	550V-600V	HP	10
UL degree of protection	Type 1, 12K, 4, 4X		
Mechanical features			
Weight	g 760		
Ambient conditions			
Operating temperature	min	°C	-25
	max	°C	+60
Storage temperature	min	°C	-40
	max	°C	+70
Resistance & Protection			
IEC degree of protection	IP65		
ETIM classification	EC001037 - Motor starter/Motor starter combination		
ETIM 8.0			