



Product designation

Direct-on-line  
starter

Product type designation

M2P03212...B4

**Electrical features**

Relay adj range	A	24-32
-----------------	---	-------

IEC technical characteristics ( $\leq 440V$ )

$I_e$	A	32
kW	kW	15

**Components**

Starter enclosure standard supplied	M2PA
-------------------------------------	------

Contactors standard supplied	BF3200A
------------------------------	---------

Thermal relay standard supplied	RF383200
---------------------------------	----------

**UL technical data**

Maximum UL/CSA horsepower ratings single-phase

110V-120V	HP	3
220V-240V	HP	7.5

Maximum UL/CSA horsepower ratings three-phase, 3-pole

200V-208V	HP	10
220V-240V	HP	10
440V-480V	HP	20
550V-600V	HP	25

**Mechanical features**

Weight	g	1300
--------	---	------

**Ambient conditions**

Operating temperature

min	°C	-25
max	°C	+60


Storage temperature

min	°C	-40
max	°C	+70

**Resistance & Protection**

Frontal IP degree	IP65
-------------------	------

**Dimensions**



Wiring diagrams



I = Start; O = Stop/Reset

**Certifications and compliance**

Compliance

IEC/EN 60947-1  
IEC/EN 60947-4-1  
UL508 CSA C22.2 n° 14

Certificates

CSAus  
cULus  
EAC

**ETIM classification**

ETIM 8.0

EC001037 -  
Motor  
starter/Motor  
starter  
combination