



| | | | | |
|---|-----|----|-------|--|
| Product designation | | | | Direct-on-line starter |
| Product type designation | | | | M1R00912...A9 |
| Electrical features | | | | |
| Relay adj range | | | A | 6.3-10 |
| IEC technical characteristics ($\leq 440V$) | | | | |
| | le | A | 10 | |
| | kW | kW | 3...4 | |
| Components | | | | |
| Starter enclosure standard supplied | | | | M1RA |
| Contactora standard supplied | | | | BF0910A |
| Thermal relay standard supplied | | | | RF381000 |
| Mechanical features | | | | |
| Weight | | | g | 995 |
| Ambient conditions | | | | |
| Operating temperature | | | | |
| | min | °C | -25 | |
| | max | °C | +60 | |
| Storage temperature | | | | |
| | min | °C | -40 | |
| | max | °C | +70 | |
| Resistance & Protection | | | | |
| Frontal IP degree | | | | IP65 |
| ETIM classification | | | | |
| ETIM 8.0 | | | | EC001037 - Motor starter/Motor starter combination |