



Enclosed star-
delta starters
M3P02670

Product designation

Product type designation

Electrical features

Maximum operating current ($\leq 440V$) A 43

Components

Starter enclosure standard supplied M3PA70

Contactor standard supplied BF2600A,
BF2600A,
BF1810A

Thermal relay to purchase separately RF38...

Auxiliary contact standard supplied BFX1020,
BFX1011,
BFX1011

Contact characteristics

IEC standard motor powers

230V	kW	11
400V	kW	22
440V	kW	22
500V	kW	25

Mechanical features

Weight g 3650

Ambient conditions

Operating temperature

min	°C	-25
max	°C	+60

Storage temperature




min	°C	-40
max	°C	+70

Resistance & Protection


Frontal IP degree IP65

Dimensions



STAR-DELTA STARTER, ENCLOSED STARTER, WITH START AND STOP/RESET BUTTONS.
STARTING TIME UP TO 12 SECONDS AND A MAXIMUM OF 30 OPERATIONS/HOUR, MAX IEC
OPERATING CURRENT 43A. COIL VOLTAGE 230VAC 50/60HZ



Drilling for surface fixing



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14
for starters
IEC/EN 60947-1
IEC/EN 60947-4-1
UL508

Certificates

/

ETIM classification

ETIM 8.0

EC001037 -
Motor
starter/Motor
starter
combination