



Product designation

Direct-on-line starter

Product type designation

M3P06512...B7

Electrical features

Relay adj range	A	45-65
IEC technical characteristics ($\leq 440V$)	le	A 65
	kW	kW 30

Components

Starter enclosure standard supplied	M3PA
Contactor standard supplied	BF6500A
Thermal relay standard supplied	RF826500

UL technical data

Maximum UL/CSA horsepower ratings three-phase, 3-pole	200V-208V	HP	20
	220V-240V	HP	25
	440V-480V	HP	50
	550V-600V	HP	60

Mechanical features

Weight	g	3760
--------	---	------

Ambient conditions

Operating temperature	min	°C	-25
	max	°C	+60


Storage temperature

min	°C	-40
max	°C	+70


Resistance & Protection

Frontal IP degree	IP65
-------------------	------

Dimensions



Wiring diagrams



I = Start; O = Stop/Reset

Certifications and compliance

Certificates

EAC

ETIM classification

ETIM 8.0

EC001037 -
Motor
starter/Motor
starter
combination