



Direct-on-line  
starter  
M3R06512...B7

Product designation

Product type designation

**Electrical features**

Relay adj range	A	46-65
IEC technical characteristics ( $\leq 440V$ )	le	A 65
	kW	kW 30

**Components**

Starter enclosure standard supplied	M3RA
Contactor standard supplied	BF6500A
Thermal relay standard supplied	RF826500

**Mechanical features**

Weight	g	3410
--------	---	------

**Ambient conditions**

Operating temperature	min	°C	-25
	max	°C	+60



Storage temperature

min	°C	-40
max	°C	+70


**Resistance & Protection**

Frontal IP degree	IP65
-------------------	------


**Dimensions**



Drilling for surface fixing



**Wiring diagrams**



R = Reset; I = Start; O = Stop

### Certifications and compliance

#### Compliance

IEC/EN 60947-1  
IEC/EN 60947-4-1  
UL508 CSA C22.2 n° 14

#### Certificates

EAC

### ETIM classification

ETIM 8.0

EC001037 -  
Motor  
starter/Motor  
starter  
combination