DMED100T1

ENERGY METER, SINGLE-PHASE, NON EXPANDABLE, DIGITAL WITH LCD DISPLAY, 40A DIRECT CONNECTION, 1U, 1 PULSE OUTPUT, 220...240VAC

Auxiliary supply Us			
Operational frequency			
	min	Hz	50
	max	Hz	60
Rated frequency		Hz	50
Power consumption			
	Max	VA	7
Power dissipation Max		W	0.45
Measuring voltage inputs			
Rated voltage (Ue)			
	phase-neutral	VAC	220…240
Operating voltage range			
	phase-neutral	VAC	184…264
Connection method			Direct
Current			
IEC maximum (Imax)		A	40
IEC minimum (Imin)		A	0.25
IEC rated (Iref-Ib)		A	5
IEC start (Ist)		mA	20
Transition (Itr)		A	0.5
Accuracy			
	Active energy		Class 1 (IEC/EN 62053-21)
Output characteristics			
LED Pulse rate		pulse/kWh	1000
LED Pulse duration		ms	30
Static output pulse rate		pulse/kWh	10
Static output pulse duration		ms	100
Static output external voltage		VDC	10...30
Static outputs Maximum current		mA	50
Insulations			
Rated insulation voltage Ui IEC/EN		V	250
Rated impulse withstand voltage Uimp		kV	6
Operating frequency withstand voltage		kV	4
Mechanical features			
Housing type			Polyamide
Terminals type			Fixed
Conductor cross section			
	min	mm²	1.5
	Max	mm²	10
	min	AWG	16
	Max	AWG	6
Tightening torque (Max)			
		Nm	1.5
		lbin	14

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding

DMED100T1

ENERGY METER, SINGLE-PHASE, NON EXPANDABLE, DIGITAL WITH LCD DISPLAY, 40A DIRECT CONNECTION, 1U, 1 PULSE OUTPUT, 220...240VAC

Fixing				Din rail
Weight			g	86
Ambient conditions				
Temperature				
	Operating temperature			
		min	°C	-25
		max	°C	+55
	Storage temperature			
		min	°C	-25
		max	°C	+70
Relative humidity			%	<80
Max altitude			m	2000
Maximum Pollution degree				2
Overvoltage category				III
Mechanical environment				Class M1
Magnetic environment				Class E2

Dimensions



Wiring diagrams



Certifications and compliance

Compliance	
	CSA 22.2 n°61010-1
	EN 50470-1
	IEC/EN 61010-1
	UL61010-1
Certificates	
	cULus
	EAC

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding

RCM

ETIM classification

ETIM 8.0	EC001506 - Kilowatt-hour meter

The characteristics described in this document are subject to updates or modifications at any time. The descriptions, technical and functional information, illustrations and instructions in this brochure are purely illustrative, and are consequently not contractually binding