



Product designation

Direct-on-line starter

Product type designation

M2P03212...B4

**Electrical features**

Relay adj range	A	24-32
IEC technical characteristics ( $\leq 440V$ )		
	le	A
	kW	kW
		32
		15

**Components**

Starter enclosure standard supplied	M2PA
Contactor standard supplied	BF3200A
Thermal relay standard supplied	RF383200

**UL technical data**

Maximum UL/CSA horsepower ratings single-phase			
	110V-120V	HP	3
	220V-240V	HP	7.5
Maximum UL/CSA horsepower ratings three-phase, 3-pole			
	200V-208V	HP	10
	220V-240V	HP	10
	440V-480V	HP	20
	550V-600V	HP	25

**Mechanical features**

Weight	g	1300
--------	---	------

**Ambient conditions**

Operating temperature			
	min	°C	-25
	max	°C	+60


Storage temperature

	min	°C	-40
	max	°C	+70

**Resistance & Protection**

Frontal IP degree	IP65
-------------------	------

**Dimensions**



Wiring diagrams



I = Start; O = Stop/Reset

### Certifications and compliance

#### Compliance

IEC/EN 60947-1  
IEC/EN 60947-4-1  
UL508 CSA C22.2 n° 14

#### Certificates

CSAus  
cULus  
EAC

### ETIM classification

ETIM 8.0

EC001037 -  
Motor  
starter/Motor  
starter  
combination