



Product designation

Direct-on-line starter

Product type designation

M2P03212...B4

Electrical features

Relay adj range	A	24-32
IEC technical characteristics ($\leq 440V$)		
	le	A
	kW	kW
		32
		15

Components

Starter enclosure standard supplied	M2PA
Contactor standard supplied	BF3200A
Thermal relay standard supplied	RF383200

UL technical data

Maximum UL/CSA horsepower ratings single-phase			
	110V-120V	HP	3
	220V-240V	HP	7.5
Maximum UL/CSA horsepower ratings three-phase, 3-pole			
	200V-208V	HP	10
	220V-240V	HP	10
	440V-480V	HP	20
	550V-600V	HP	25

Mechanical features

Weight	g	1300
--------	---	------

Ambient conditions

Operating temperature			
	min	°C	-25
	max	°C	+60


Storage temperature

	min	°C	-40
	max	°C	+70

Resistance & Protection

Frontal IP degree	IP65
-------------------	------

Dimensions



Wiring diagrams



I = Start; O = Stop/Reset

Certifications and compliance

Compliance

IEC/EN 60947-1
IEC/EN 60947-4-1
UL508 CSA C22.2 n° 14

Certificates

CSAus
cULus
EAC

ETIM classification

ETIM 8.0

EC001037 -
Motor
starter/Motor
starter
combination