



Modular LCD
multimeters. non
expandable
DMG210
Three-phase +
neutral
4

Product designation

Product type designation

Type

DIN rail module number

Auxiliary supply U_s

Auxiliary rated supply voltage AC	VAC	100...240		
Auxiliary rated supply voltage DC	VDC	110...250		
Auxiliary operating voltage range	AC	min	VAC	85
		Max	VAC	264
	DC	min	VDC	93.5
		Max	VDC	300

Operational frequency

min	Hz	45
max	Hz	66

Power consumption

Max	VA	4.5
-----	----	-----

Power dissipation Max

W	1.7
---	-----

Measuring voltage inputs

Rated voltage (U_e)

phase-phase	VAC	690
phase-neutral	VAC	400

Operating voltage range

phase-phase	VAC	20...830
phase-neutral	VAC	10...480

Voltage inputs operational frequency

min	Hz	45
max	Hz	66

Voltage inputs measurement method

True RMS

Connection method

Single. two.
three-phase with
or without neutral.
balanced three-
phase systems

Current inputs

Rated current (I_e)

A	5
---	---

Measurement range

0.01...6


Measurement method

TRMS

Overload capacity


+20% I_e through
external CT with
5A secondary

Overload peak		A	50A for 1s
Accuracy			
	VLN voltage		±0.5%
	VLL voltage		±0.5%
	Current		±0.5%
	Frequency		±0.05%
	Active power		±1%
	Active energy		Class 1 (IEC/EN 62053-21)
	Reactive energy		Class 2 (IEC/EN 62053-23)
RS485 serial interface			
Baud rate		bps	Programmable 1200...38400
Insulations			
Rated insulation voltage Ui IEC/EN		V	690
Rated impulse withstand voltage Uimp		kV	9.5
Operating frequency withstand voltage		kV	5.2
Functions			
Harmonic analysis			THD only
PLC logic			No
Type of communication port			RS485
Ethernet-RS485 gateway function			No
Mechanical features			
Housing type			Polyamide
Terminals type			Fixed
Conductor cross section			
	min	mm ²	0.2
	Max	mm ²	4
	min	AWG	24
	Max	AWG	12
Tightening torque (Max)		Nm	0.8
		lbin	7
Fixing			Din rail
Weight		g	300
Ambient conditions			
Temperature			
	Operating temperature		
		min	°C -20
		max	°C +60
	Storage temperature		
		min	°C -30
		max	°C +80
Relative humidity		%	<90
Maximum Pollution degree			2
Protection degree			IP30
Dimensions			




Wiring diagrams


Single-phase





Two-phase




Three-phase with or without neutral



Three-phase without neutral in ARON connection



Balanced 3-phase connection with or without neutral



CODE	AUX SUPPLY
DMG100-110-200-210-300	100...240VAC 110...250VDC
DMG6...	100...440VAC 110...250VDC
DMG7000-7500-8000-9000	100...240VAC 110...250VDC



Certifications and compliance

Compliance

CSA C22.2 n°14

IEC/EN 61000-6-2

IEC/EN 61000-6-4

IEC/EN 61010-1

UL508

Certificates

cULus

EAC

GOST

RCM

ETIM classification

ETIM 8.0

EC002301 -
Multifunction
measuring
instrument