



Direct-on-line
starter
M3R08012...B8

Product designation

Product type designation

Electrical features

Relay adj range	A	60-82
IEC technical characteristics ($\leq 440V$)	le kW	A kW
		80 37...45

Components

Starter enclosure standard supplied	M3RA
Contactor standard supplied	BF8000A
Thermal relay standard supplied	RF828200

Mechanical features

Weight	g	3410
--------	---	------



Ambient conditions

Operating temperature	min	°C	-25
	max	°C	+60
Storage temperature	min	°C	-40
	max	°C	+70


Resistance & Protection

Frontal IP degree	IP65
-------------------	------


Dimensions



Drilling for surface fixing



Wiring diagrams



R = Reset; I = Start; O = Stop

Certifications and compliance

Compliance

IEC/EN 60947-1
 IEC/EN 60947-4-1
 UL508 CSA C22.2 n° 14

Certificates

EAC

ETIM classification

ETIM 8.0

EC001037 -
 Motor
 starter/Motor
 starter
 combination